




EE811



Presence detector 360°, 2 channels, flush mounted, white

Technical characteristics

Main electrical features

Rated operational voltage Ue	230 V
Frequency	50 Hz

Dimensions

Width of installed product	100 mm
Recommended installation height	2.5...3.5 m

Measurement

Detection Method	Passive Infrared
------------------	------------------

Power supply

Supply voltage	230 V
----------------	-------

Detection

Detection angle	360 °
Detection angle	360 °
Detection field Ø, on floor	≈ 12 m
Detection field Ø, at desk height	≈ 5 m
Frontal detecting distance	7 m
Side detecting distance	13 m

Materials

Colour	pure white
RAL colour	RAL 9010 - Pure white
Material	plastic

Lighting control

Response brightness, adjustable	≈ 5...1200 lx
Brightness measurement range	5 / 1200 Lux

Installation, mounting

Maximum Mounting Height	4 m
-------------------------	-----

Settings

Response value sensitivity adjustable	Yes
Delay time, adjustable	≈ 1...30 mn

Equipment

Angle of horizontal detection	360 °
Slewing	Detector head slewing by 90°

Safety

Protection class	isol.class II
------------------	---------------

Use conditions

Operating temperature	0...45 °C
-----------------------	-----------

Storage/transport temperature	-10...60 °C
-------------------------------	-------------

Identification

Application, usage	Motion detector
--------------------	-----------------

Main design line	Motion detectors
------------------	------------------