



EE870



IP55

IP55 Motion Detector Comfort 220/360° White

Technical characteristics

Architecture

Bus system Without

Functions

Function Presence simulation ; can be used as a single unit, main device or extension unit

Operating mode with 2 operating modes: time- and light-dependent switch on or pulse mode

Main electrical features

Frequency 50/60 Hz

Voltage

Operating voltage 230 V~ +10%/-15%

Dimensions

Height of installed product 2.5 m

Length 153 mm

Recommended installation height 2.5 m

Power

Power consumption (standby) ≈ 1.2 W

Incandescent bulb power 2300 W

Measurement

Detection field, semi-circular shaped ≈ 10 x 20 m

Reach distance

Range, side each ≈ 10 m

Camera

Lens Lens setting horizontal ± 80° ; Lens setting vertical - 30 ... +90°

Power supply

Supply voltage 230 V AC

Detection

Detection angle 220 / 360 °

Detection angle 360 °

Detection angle 220 °

Detection field Ø, on floor ≈ 6 m

Materials

Colour	white
--------	-------

Lighting control

Response brightness, adjustable	≈ 5...1000 lx
---------------------------------	---------------

Brightness measurement range	5 / 1000 Lux
------------------------------	--------------

Fluorescent lamps with electronical ballast (EB)	580 W
--	-------

Fluorescent bulbs control

Energy-saving lamps	20 x 20 W
---------------------	-----------

Fluorescent lamps parallel compensated	400 W /47 µF
--	--------------

LED control

230V LED lamps	20 x 20 W
----------------	-----------

LED	with LED detection and mode indicator
-----	---------------------------------------

Incandescent bulbs control

12 V halogen lamps	1500 W
--------------------	--------

230 V incandescent lamps and halogen lamps	2300 W
--	--------

Installation, mounting

Maximum Mounting Height	4 m
-------------------------	-----

Connection

Connection type	quick connect
-----------------	---------------

Type of contacts	contact floating
------------------	------------------

Type of connection	with screw terminals
--------------------	----------------------

Cable

Wire	with cable entry
------	------------------

Settings

Response value sensitivity adjustable	Yes
---------------------------------------	-----

Response sensitivity, settable	20...100 %
--------------------------------	------------

Time delayed range	5s to 30 min
--------------------	--------------

Delay time, adjustable	5 s...30 mn
------------------------	-------------

Setting	with potentiometers for fine adjustment of the response brightness, sensitivity and delay time
---------	--

Scope of delivery

Component	with fitting material
-----------	-----------------------

Equipment

Potential-free	with potential-free contact
----------------	-----------------------------

Slewing	vertically slewing and horizontally rotating
---------	--

Safety

Protection class	isol.class II
------------------	---------------

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Use conditions

Operating temperature	-20...55 °C
-----------------------	-------------

Storage/transport temperature	-20...60 °C
-------------------------------	-------------

Energy-saving

low intrinsic energy requirement ; energy saving by means of presence and brightness-dependent ON and OFF switching of light

Identification

Application, usage	Motion detector
--------------------	-----------------

Main design line	Motion detectors
------------------	------------------