



CD280S

**RCCB 2P 80A 30mA AC Class 60Hz**

**Technical characteristics**

**Architecture**

Neutral position	right
Number of poles	2 P
Type of pole	2 P

**Configuration**

Number of modules	2
-------------------	---

**Main electrical features**

Type of supply voltage	AC
Frequency	60 Hz

**Voltage**

Rated impulse withstand voltage	4000 V
---------------------------------	--------

**Electric current**

Rated residual operating current	30 mA
Rated current	80 A
Withstand not tripping on 8-20 $\mu$ s wave	0.25 kA
Breaking and opening capacity	1500 A
Rated conditional short-circuit current Inc according to EN 61008-1	6 kA

**Electric current / temperature**

Rating current -25°C	80 A
Rating current -20°C	80 A
Rating current -15°C	80 A
Rating current -10°C	80 A
Rating current -5°C	80 A
Rating current 0°C	80 A
Rating current 5°C	80 A
Rating current 10°C	80 A
Rating current 15°C	80 A
Rating current 20°C	80 A
Rating current 25°C	80 A
Rating current 30°C	80 A
Rating current 35°C	80 A
Rating current 40°C	80 A
Rating current 45°C	80 A
Rating current 50°C	80 A

Rating current 55°C	80 A
Rating current 60°C	74 A
Rating current 65°C	66 A
Rating current 70°C	56 A
<b>Dimensions</b>	
Depth of installed product	70 mm
Height of installed product	83 mm
Width of installed product	35 mm
Construction size (DIN 43880)	3
<b>Frequency</b>	
Frequency	60 Hz
<b>Power</b>	
Total power loss under IN	9.1 W
<b>Tripping</b>	
Short-time delayed tripping	No
<b>Endurance</b>	
Electric endurance in number of cycles	2000
Number of mechanical operations	4000
<b>Installation, mounting</b>	
Tightening torque	3,3Nm
Type of bottom rail clip for modular devices	metallic
Top removability for modular devices	No
Bottom removability for modular devices	No
<b>Equipment</b>	
Type selective	No
Can be accessorized	Yes
With transparent product label holder	No
<b>Standards</b>	
European directive WEEE	not concerned
<b>Safety</b>	
Protection index IP	IP20
Residual current type	AC
<b>Use conditions</b>	
Operating temperature	-25...40 °C
Degree of pollution according to IEC 60664 / IEC 60947-2	2
Altitude	2000 m
Storage/transport temperature	-55...70 °C