




EE883



IP54

Circulation sensor HF 360°, IP54, wall mounted, white

Technical characteristics

Architecture

Fixing mode surface-mounting

Connectivity

Receiver category 2

Main electrical features

Frequency 50 Hz

Electric current

Switching current 10 A

Dimensions

Height of installed product 2500 mm

Dimensions (Ø x H) 125.5 x 51 mm

Width of installed product 123 mm

Recommended installation height 2.5 m

Detection

Detection angle 360 °

Detection field Ø, on floor 8 m

Frontal detecting distance 4 m

Side detecting distance 4 m

Materials

Colour white

RAL colour RAL 9010 - Pure white

Material PC-ABS

Lighting control

Response brightness, adjustable 2...1000 lx

Brightness measurement range 2 / 1000 Lux

Installation, mounting

Maximum Mounting Height 4 m

Mounting type surface-mounted

Settings

Response value sensitivity adjustable Yes

Delay time, adjustable 5 s...15 mn

Setting

with potentiometers for fine adjustment of the response brightness, sensitivity and delay time

Scope of delivery

Component

with fitting material

Safety

Protection class

isol.class II

Use conditions

Operating temperature

-20...50 °C

Storage/transport temperature

-35...70 °C (storage at > 45°C reduces the service life)

Identification

Application, usage

Motion detector

Main design line

Motion detectors