



EH010



Daily time switch 1 channel, 16A, 1 module

Technical characteristics

Functions

Number of function channels	1
Switching cycles	min. 30000
Slide switch	with slide switch for permanent on/automatic

Configuration

Switch mode	NO contact
Number of modules	1

Main electrical features

Frequency	50 Hz
-----------	-------

Voltage

Operating voltage	230 V~
-------------------	--------

Electric current

Max. power with cos phi 0.6	3 A
Switching current at cos φ = 0.6	max. 3 A

Dimensions

Depth of installed product	60 mm
Height of installed product	80 mm
Width of installed product	18 mm
Width of rail mounted device (RMD)	1 modules

Power

Power consumed	0.5 VA
Power consumption (operation)	0.5 VA
Total power loss under IN	1 W
Loss power at full load	≈ 1 W
Power dissipation per coil	0.5 W

Fluorescent bulbs control

Compact fluorescent lamps	max. 100 W
---------------------------	------------

Incandescent bulbs control

Max. power with incandescent lamps	900 W
230 V incandescent lamps and halogen lamps	max. 900 W

Installation, mounting

Mounting type	din-Rail
Installation mode	for mounting on DIN rail
Connection	
Connection cross-sect. flexible conductor	1 / 6mm ²
Connection cross-sect. rigid cable	1,5 / 10mm ²
Conductor cross-section (flexible)	1...6 mm ²
Conductor cross-section (rigid)	1.5...10 mm ²
Number of contacts	1
Type of contacts	1 changeover
Type of connection	with screw terminals
Contact	with potential-free switching contact
Type of connection	with screw
Settings	
Number of program steps	96
Summer / Winter time change	manual
Shortest switching time	15 mn
Type of programming	analog
Program cycles	Programme cycle: 24 hours
Programming cycle	24H
Setting	Setting via day dial
Equipment	
Number of channels	1
Number of switching times for on/off	96
Supply failure reserve	without
Switching cycles at $\cos \varphi = 0,6$	min. 30000
Use	
Cycle	daily
Safety	
REACH conform	No
RoHS conform	Yes
Halogen free	No
Use conditions	
Operating temperature	-10...55 °C
Working accuracy	1
Storage/transport temperature	-20...70 °C
Identification	
Main design line	Light control