



DR32F



## Din rail board, 2 row 32M, non-transparent door, flush

### Technical characteristics

#### Architecture

Intended door position left

#### Configuration

Number of modules 32

#### Compatibility

Suitable for lightning protection Yes

#### Dimensions

Insertion depth 110 mm

Depth of wall niche 105 mm

Depth of installed product 5 mm

Internal depth 107 mm

Height of installed product 499 mm

Installation height 470 mm

Width of installed product 430 mm

Width in division units 16

Thickness of sidewall material 1.2 mm

Built-in width 400 mm

#### Cover, door

Material thickness cover 1.2 mm

Identification of protection index 40

Interlockable No

Number of keylock of the door 0

Cover type Closed (plain)

Door leave single

Cover type Cover

Transparent cover or door No

#### Materials

Copper weight of the product 0 kg

Colour light grey

Material quality Steel

Surface appearance matt

#### Installation, mounting

Suitable for outdoor use No

Suitable for ground mounting No

**Settings**

Enclosure type	Distributor empty cabinet
----------------	---------------------------

**Equipment**

Number of rows	2
Number of keys	1
Quantity of rails	2
On/Off switch	No
Can be accessorized	Yes
Number of openings for flange plates	2
Extension possible	Yes
Earthing terminal block	No
Neutral terminal block	Yes

**Standards**

Approvals	BS EN 61439-3
European directive WEEE	not concerned

**Safety**

IK protection code against mechanical impacts	IK05
Protection class	isol.class I
Glow wire test	according to IEC 61439-1
RoHS conform	Yes
Halogen free	No
Fire resistance	-