



ERC225

Override Contactor 25A, 2NO, 230V~50/60Hz

Technical characteristics

Architecture

Number of poles	2 P
-----------------	-----

Configuration

Number of modules	1
-------------------	---

Main electrical features

Rated operational voltage Ue	230 V
Frequency	50 Hz

Voltage

Rated insulation voltage	250 V
DC control voltage	0 V
Command voltage AC	230 V
Rated impulse withstand voltage	4 kV

Electric current

Rated current	25 A
Thermal rated current outside of housings	25 A
Acceptable current load with AC7 category A	25 A
Acceptable current load with AC7 category B	8.5 A

Dimensions

Depth of installed product	60 mm
Height of installed product	83 mm
Width of installed product	17.85 mm

Power

Inrush power absorbed	7.4 W
Operating consumption	1.8 W
Total power loss under IN	3.6 W
Power loss per contact	1.5 W
Power dissipation per coil	0.6 W
Contact rating with 230 V in AC7 category A	4.6 kW
Contact rating with 230 V in AC7 category B	880 W

Tripping

Time of response when opening	15 ms
Time of response when closing	25 ms

Resistance

Winding resistance	5500 Ω
--------------------	--------

Endurance

Electric endurance in number of cycles	30000
--	-------

Number of mechanical operations	1000000
---------------------------------	---------

Fluorescent bulbs control

Max. power with fluorescent parallel lamps	500 VA
--	--------

Fluorescent lamps in duo circuit	990 VA
----------------------------------	--------

Max. load fluorescent lamp	490 VA
----------------------------	--------

Incandescent bulbs control

Max. power with incandescent lamps	1100 W
------------------------------------	--------

Connection

Number of contacts	2
--------------------	---

Connection cross-section of the control cable solid	1 / 10 mm ²
---	------------------------

Equipment

Can be accessorized	Yes
---------------------	-----

Use

Local operation/hand operation	Yes
--------------------------------	-----

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

Protection index IP	IP2X
---------------------	------

Protection class	isol.class II
------------------	---------------

Use conditions

Operating temperature	-10...50 °C
-----------------------	-------------

Storage/transport temperature	-40...80 °C
-------------------------------	-------------