



ESC126

Contactor 25A, 1NC, 230V~50/60Hz

Technical characteristics

Architecture

Number of poles	1 P
-----------------	-----

Configuration

Number of modules	1
-------------------	---

Main electrical features

Rated operational voltage Ue	230 V
------------------------------	-------

Frequency	50 Hz
-----------	-------

Voltage

Rated insulation voltage	250 V
--------------------------	-------

DC control voltage	0 V
--------------------	-----

Command voltage AC	230 V
--------------------	-------

Rated impulse withstand voltage	4 kV
---------------------------------	------

Electric current

Rated current	25 A
---------------	------

Thermal rated current outside of housings	25 A
---	------

Acceptable current load with AC7 category A	25 A
---	------

Acceptable current load with AC7 category B	8.5 A
---	-------

Dimensions

Depth of installed product	60 mm
----------------------------	-------

Height of installed product	83 mm
-----------------------------	-------

Width of installed product	17.85 mm
----------------------------	----------

Power

Inrush power absorbed	7.4 W
-----------------------	-------

Operating consumption	1.8 W
-----------------------	-------

Total power loss under IN	1.5 W
---------------------------	-------

Power loss per contact	1.5 W
------------------------	-------

Power dissipation per coil	0.6 W
----------------------------	-------

Contact rating with 230 V in AC7 category A	4.6 kW
---	--------

Contact rating with 230 V in AC7 category B	880 W
---	-------

Tripping

Time of response when opening	15 ms
-------------------------------	-------

Time of response when closing	25 ms
-------------------------------	-------

Resistance

Winding resistance	5500 Ω
--------------------	---------------

Endurance

Electric endurance in number of cycles	30000
--	-------

Number of mechanical operations	1000000
---------------------------------	---------

Fluorescent bulbs control

Max. power with fluorescent parallel lamps	500 VA
--	--------

Fluorescent lamps in duo circuit	990 VA
----------------------------------	--------

Max. load fluorescent lamp	490 VA
----------------------------	--------

Incandescent bulbs control

Max. power with incandescent lamps	1100 W
------------------------------------	--------

Connection

Number of contacts	1
--------------------	---

Type of contacts	INC
------------------	-----

Connection cross-section of the control cable solid	1 / 10 mm ²
---	------------------------

Equipment

Can be accessorized	Yes
---------------------	-----

Use

Local operation/hand operation	No
--------------------------------	----

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

Protection index IP	IP2X
---------------------	------

Protection class	isol.class II
------------------	---------------

Use conditions

Operating temperature	-10...50 °C
-----------------------	-------------

Storage/transport temperature	-40...80 °C
-------------------------------	-------------
