



EC100

**Hours counter**

**Technical characteristics**

**Configuration**

Number of modules	2
-------------------	---

**Main electrical features**

Frequency	50 Hz
-----------	-------

**Dimensions**

Depth of installed product	60 mm
Height of installed product	90 mm
Width of installed product	35 mm
Front plate height	90 mm
Front plate width	35 mm

**Power**

Total power loss under IN	1.5 W
---------------------------	-------

**Power supply**

Supply voltage	230 V +/- 15%
----------------	---------------

**Installation, mounting**

Mounting type	din-Rail
---------------	----------

**Connection**

Connection cross-sect. flexible conductor	1 / 6mm <sup>2</sup>
Connection cross-sect. rigid cable	1,5 / 10mm <sup>2</sup>
Type of connection	with screw

**Equipment**

Reading unit	1 h
Digits number	6

**Safety**

REACH conform	Yes
RoHS conform	Yes

**Use conditions**

Operating temperature	-10...45 °C
Storage/transport temperature	-20...60 °C