



ESC126

**Contactors 25A, 1NC, 230V~50/60Hz**

**Technical characteristics**

**Architecture**

Type of order	Not applicable
Number of poles	1 P

**Configuration**

Number of modules	1
-------------------	---

**Main electrical features**

Rated operational voltage Ue	230 V
Frequency	50 Hz

**Voltage**

Rated insulation voltage	250 V
DC control voltage	0 V
Command voltage AC	230 V
Rated impulse withstand voltage	4 kV

**Electric current**

Rated current	25 A
Thermal rated current outside of housings	25 A
Acceptable current load with AC7 category A	25 A
Acceptable current load with AC7 category B	8.5 A

**Dimensions**

Depth of installed product	60 mm
Height of installed product	83 mm
Width of installed product	17.85 mm

**Power**

Inrush power absorbed	7.4 W
Operating consumption	1.8 W
Total power loss under IN	1.5 W
Power loss per contact	1.5 W
Power dissipation per coil	0.6 W
Contact rating with 230 V in AC7 category A	4.6 kW
Contact rating with 230 V in AC7 category B	880 W

**Tripping**

Time of response when opening	15 ms
-------------------------------	-------

Time of response when closing	25 ms
-------------------------------	-------

#### Resistance

Winding resistance	5500 Ω
--------------------	--------

#### Endurance

Electric endurance in number of cycles	30000
Number of mechanical operations	1000000

#### Fluorescent bulbs control

Max. power with fluorescent parallel lamps	500 VA
Fluorescent lamps in duo circuit	990 VA
Max. load fluorescent lamp	490 VA

#### Incandescent bulbs control

Max. power with incandescent lamps	1100 W
------------------------------------	--------

#### Installation, mounting

Tightening torque	1,2Nm
-------------------	-------

#### Connection

Connection cross-sect. flexible conductor	1 / 6mm <sup>2</sup>
Connection cross-sect. rigid cable	1 / 10mm <sup>2</sup>
Number of contacts	1
Type of contacts	1NC
Type of connection	with screw
Connection cross-section of the control cable solid	1 / 10 mm <sup>2</sup>

#### Equipment

Can be accessorized	Yes
---------------------	-----

#### Use

Local operation/hand operation	No
--------------------------------	----

#### Standards

European directive WEEE	not concerned
-------------------------	---------------

#### Safety

Protection class	isol.class II
------------------	---------------

#### Use conditions

Operating temperature	-10...50 °C
Storage/transport temperature	-40...80 °C