



ESC428S

**Humfree Contactor 25A, 3NO+1NC, 230V~50/60Hz**

**Technical characteristics**

**Architecture**

Type of order	Not applicable
Number of poles	4 P

**Configuration**

Number of modules	2
-------------------	---

**Main electrical features**

Rated operational voltage Ue	400 V
Frequency	50/60 Hz

**Voltage**

Rated insulation voltage	440 V
DC control voltage	0 V
Command voltage AC	230 V
Rated impulse withstand voltage	4 kV

**Electric current**

Rated current	25 A
Thermal rated current outside of housings	25 A
Acceptable current load with AC7 category A	25 A
Acceptable current load with AC7 category B	8.5 A

**Dimensions**

Depth of installed product	60 mm
Height of installed product	83 mm
Width of installed product	35.75 mm

**Power**

Inrush power absorbed	2.9 W
Operating consumption	2.9 W
Total power loss under IN	7.4 W
Power loss per contact	1.5 W
Power dissipation per coil	2.9 W
Contact rating with 230 V in AC7 category A	4.6 kW
Contact rating with 230 V in AC7 category B	880 W
Contact rating with 400 V in AC7 category A	13.8 kW
Contact rating with 400 V in AC7 category B	2.6 kW

<b>Tripping</b>	
Time of response when opening	15 ms
Time of response when closing	25 ms
<b>Resistance</b>	
Winding resistance	14700 Ω
<b>Endurance</b>	
Electric endurance in number of cycles	30000
Number of mechanical operations	1000000
<b>Fluorescent bulbs control</b>	
Max. power with fluorescent parallel lamps	500 VA
Fluorescent lamps in duo circuit	990 VA
Max. load fluorescent lamp	490 VA
<b>Incandescent bulbs control</b>	
Max. power with incandescent lamps	1100 W
<b>Installation, mounting</b>	
Tightening torque	1,2Nm
<b>Connection</b>	
Connection cross-sect. flexible conductor	1 / 6mm <sup>2</sup>
Connection cross-sect. rigid cable	1 / 10mm <sup>2</sup>
Number of contacts	4
Type of contacts	3NO+1NC
Type of connection	with screw
Connection cross-section of the control cable solid	1 / 10 mm <sup>2</sup>
<b>Equipment</b>	
Can be accessorized	Yes
<b>Use</b>	
Local operation/hand operation	No
<b>Standards</b>	
European directive WEEE	not concerned
<b>Safety</b>	
Protection class	isol.class II
<b>Use conditions</b>	
Operating temperature	-10...50 °C
Storage/transport temperature	-40...80 °C