



ECN140D



**1 Phase kWhmeter direct 40A 1M**

**Technical characteristics**

**Architecture**

Number of poles	2 P
Type of pole	1P+N

**Functions**

Precision class	B
Tarif type	One-tariff

**Configuration**

Number of modules	1
-------------------	---

**Compatibility**

Suitable for	Purchase
--------------	----------

**Main electrical features**

Rated operational voltage Ue	184 / 276 V
Type of supply voltage	AC
Frequency	50 Hz

**Voltage**

Max operating voltage	300 V
Rated impulse withstand voltage	6 kV

**Electric current**

Minimum operating current	0.02 A
Operating current	0.02 / 40 A
Rated current	40 A
Reference current	5 A
Max. measurement circuit current	40 A

**Dimensions**

Depth of installed product	58 mm
Height of installed product	92 mm
Width of installed product	18 mm

**Power**

Power consumed	2 VA
Total power loss under IN	1 W

**Electrical specifications**

Type of pulse generator	optical
-------------------------	---------

**Measurement**

Frequency measuring range	45 to 65 Hz
Type of measuring instrument	electrical
Principle of measurement	Direct measurement

**Power supply**

Supply voltage	230 V $\pm$ 20%
----------------	-----------------

**Installation, mounting**

Tightening torque	1Nm
Mounting type	din-Rail

**Connection**

Wire cross section of metering entrance wire	16 mm <sup>2</sup>
Wire cross section of metering outgoing wire	16 mm <sup>2</sup>

**Equipment**

Type of display	LCD
Type of counter	single-phase counter

**Standards**

Standard text	IEC 62053-21 / 23 ; IEC 61557-12
---------------	----------------------------------

**Safety**

Protection class	isol.class II
Halogen free	No

**Use conditions**

Operating temperature	-25...55 °C
Degree of pollution according to IEC 60664 / IEC 60947-2	2
Altitude	2000 m
Storage/transport temperature	-25...70 °C