



ESC463

## Contactor 63A, 4NO, 230V~50Hz

### Technical characteristics

#### Architecture

Number of poles	4 P
-----------------	-----

#### Configuration

Number of modules	3
-------------------	---

#### Main electrical features

Rated operational voltage Ue	400 V
------------------------------	-------

Frequency	50 Hz
-----------	-------

#### Voltage

Rated insulation voltage	440 V
--------------------------	-------

DC control voltage	0 V
--------------------	-----

Command voltage AC	230 V
--------------------	-------

Rated impulse withstand voltage	4 kV
---------------------------------	------

#### Electric current

Rated current	63 A
---------------	------

Thermal rated current outside of housings	63 A
---	------

Acceptable current load with AC7 category A	63 A
---	------

Acceptable current load with AC7 category B	32 A
---	------

#### Dimensions

Depth of installed product	60 mm
----------------------------	-------

Height of installed product	85 mm
-----------------------------	-------

Width of installed product	54 mm
----------------------------	-------

#### Power

Inrush power absorbed	62.5 VA
-----------------------	---------

Operating consumption	5.7 VA
-----------------------	--------

Total power loss under IN	21.5 W
---------------------------	--------

Power loss per contact	5 W
------------------------	-----

Power dissipation per coil	1.5 W
----------------------------	-------

Contact rating with 230 V in AC7 category A	11.6 kW
---	---------

Contact rating with 230 V in AC7 category B	3.3 kW
---	--------

Contact rating with 400 V in AC7 category A	35 kW
---	-------

Contact rating with 400 V in AC7 category B	10 kW
---	-------

#### Tripping

Time of response when opening	20 ms
Time of response when closing	25 ms
<b>Resistance</b>	
Winding resistance	770 Ω
<b>Endurance</b>	
Electric endurance in number of cycles	30000
Number of mechanical operations	1000000
<b>Fluorescent bulbs control</b>	
Max. power with fluorescent parallel lamps	2100 VA
Fluorescent lamps in duo circuit	4700 VA
Max. load fluorescent lamp	3000 VA
<b>Incandescent bulbs control</b>	
Max. power with incandescent lamps	6500 W
<b>Connection</b>	
Number of contacts	4
Connection cross-section of the control cable solid	1 / 2.5 mm <sup>2</sup>
<b>Equipment</b>	
Can be accessorized	Yes
<b>Use</b>	
Local operation/hand operation	No
<b>Standards</b>	
European directive WEEE	concerned
<b>Safety</b>	
Protection index IP	IP2X
Protection class	isol.class II
<b>Use conditions</b>	
Operating temperature	-10...50 °C
Storage/transport temperature	-40...80 °C