



ECP380D



### 3 Phase kWhmeter direct 80A 4M S0 MID

#### Technical characteristics

##### Architecture

Number of poles	4 P
Type of pole	3P+N

##### Functions

Precision class	B
Tarif type	T1...T2 (230 V AC) / -

##### Configuration

Number of modules	4
-------------------	---

##### Compatibility

Suitable for	Purchase / supply
--------------	-------------------

##### Main electrical features

Rated operational voltage Ue	92 / 480 V
Type of supply voltage	AC
Frequency	50 Hz

##### Voltage

Max operating voltage	300 V
Rated impulse withstand voltage	6 kV

##### Electric current

Minimum operating current	0.015 A
Operating current	0.015 / 80 A
Rated current	80 A
Reference current	5 A
Max. measurement circuit current	80 A

##### Dimensions

Depth of installed product	60 mm
Height of installed product	92 mm
Width of installed product	72 mm

##### Power

Power consumed	2 VA
Total power loss under IN	0.6 W
Plage Impulsion/KWh	1 / 200 Imp/kWh

##### Electrical specifications

**Measurement**

Frequency measuring range	45 to 65 Hz
Type of measuring instrument	electronical
Principle of measurement	Direct measurement

**Power supply**

Supply voltage	400 V $\pm$ 20%
----------------	-----------------

**Installation, mounting**

Tightening torque	2Nm
Mounting type	din-Rail

**Connection**

Wire cross section of metering entrance wire	33 mm <sup>2</sup>
Wire cross section of metering outgoing wire	33 mm <sup>2</sup>

**Settings**

Value of a pulse	100 Wh
------------------	--------

**Equipment**

Type of display	retro illuminated display
Tariff model of kilowatt-hour meter	Externa
Type of counter	4 wires counter

**Use**

Pulse duration	30 / 100 ms
----------------	-------------

**Standards**

Standard text	EN 50470-1 / 3 ; IEC 62053-21 / 23 ; IEC 61557-12
Certified product	MID (Measuring Instruments Directive)

**Safety**

Protection class	isol.class II
REACH conform	Yes
RoHS conform	Yes
Halogen free	No

**Use conditions**

Operating temperature	-25...55 °C
Degree of pollution according to IEC 60664 / IEC 60947-2	2
Altitude	2000 m
Storage/transport temperature	-25...70 °C