



EU101

Compres. control relay

Technical characteristics

Configuration

| | |
|-------------------|---|
| Number of modules | 2 |
|-------------------|---|

Main electrical features

| | |
|---------------------------------|----------|
| Rated operational voltage U_e | 230 V |
| Frequency | 50/60 Hz |

Electric current

| | |
|------------------------------------|-----|
| Acceptable current rating with AC1 | 8 A |
|------------------------------------|-----|

Dimensions

| | |
|-----------------------------|-------|
| Depth of installed product | 60 mm |
| Height of installed product | 85 mm |
| Length | 64 mm |
| Width of installed product | 35 mm |

Power

| | |
|---------------------------|-----|
| Total power loss under IN | 4 W |
|---------------------------|-----|

Measurement

| | |
|---------------------------|-------|
| Voltage measurement range | 230 V |
|---------------------------|-------|

Power supply

| | |
|----------------|---------------|
| Supply voltage | 3N, 400/230 V |
|----------------|---------------|

Installation, mounting

| | |
|---------------|----------|
| Mounting type | din-Rail |
|---------------|----------|

Connection

| | |
|---|-------------------------|
| Connection cross-sect. flexible conductor | 1 / 6mm ² |
| Connection cross-sect. rigid cable | 1,5 / 10mm ² |
| Type of contacts | 1 changeover |
| Type of connection | with screw |

Settings

| | |
|-----------|-------|
| Delay OFF | 200 s |
|-----------|-------|

Use conditions

| | |
|-------------------------------|-------------|
| Operating temperature | -20...55 °C |
| Storage/transport temperature | -40...70 °C |