



EE180

IP20

Astronomical Timeswitch 1 Channel

Technical characteristics

Functions

Number of function channels	1
Function	Keylock by means of blocking key

Configuration

Switch mode	change-over contact
Number of modules	2

Controls and indicators

Function of the pushbutton	yes
Indication / display	LC display with illumination

Main electrical features

Frequency	50/60 Hz
-----------	----------

Voltage

Operating voltage	230 V~ +/- 15%
-------------------	----------------

Electric current

Acceptable current rating with AC1	16 A
Max. power with cos phi 0.6	10 A
Switching current at cos ϕ = 0.6	max. 10 A

Dimensions

Depth of installed product	65 mm
Height of installed product	85 mm
Length	35 mm
Width of installed product	65 mm
Width of rail mounted device (RMD)	2 modules

Frequency

Frequency range	50...60 Hz
-----------------	------------

Power

Max. power with fluo uncompensated lamps	1000 VA
Power consumed	6 VA
Incandescent bulb power	0 / 2300 W
Total power loss under IN	2 W
Loss power at full load	≈ 2 W
Power dissipation per coil	0.3 W

Max. Breaking capacity for parallel compensated fluorescent tubes	400 W
---	-------

Max. Breaking capacity for row-compensated fluorescent tubes	1000 W
--	--------

Measurement

Running accuracy	± 1.5 s/day
------------------	-------------

Battery

Power reserve [years]	≈ 5 a
-----------------------	-------

Battery / storage battery	with lithium battery type: LS14250
---------------------------	------------------------------------

Power supply

Supply voltage	230 V +/- 15%
----------------	---------------

Fluorescent bulbs control

Fluorescent lamps	max. 1000 VA
-------------------	--------------

Max. power with fluorescent parallel lamps	400 VA
--	--------

Max. power fluo. duo lamp comp. series	1000 W
--	--------

Fluorescent lamps parallel compensated	400 VA
--	--------

Incandescent bulbs control

Max. power with incandescent lamps	2300 W
------------------------------------	--------

230 V incandescent lamps and halogen lamps	max. 2300 W
--	-------------

Installation, mounting

Mounting type	din-Rail
---------------	----------

Installation mode	for mounting on DIN rail
-------------------	--------------------------

Connection

Connection cross-sect. flexible conductor	1 / 6mm ²
---	----------------------

Connection cross-sect. rigid cable	1,5 / 10mm ²
------------------------------------	-------------------------

Conductor cross-section (flexible)	1...6 mm ²
------------------------------------	-----------------------

Conductor cross-section (rigid)	1...6 mm ²
---------------------------------	-----------------------

Number of contacts	1
--------------------	---

Type of contacts	1 changeover contact floating
------------------	-------------------------------

Type of connection	with screw terminals
--------------------	----------------------

Settings

Number of program steps	56
-------------------------	----

Summer / Winter time change	automatic
-----------------------------	-----------

Shortest switching time	1 mn
-------------------------	------

Programming	Programming possible without mains voltage
-------------	--

Astro program	Yes
---------------	-----

Time	with automatic summer/winter time change-over
------	---

Equipment

Number of channels	1
--------------------	---

Number of switching times for on/off	56
--------------------------------------	----

ON / OFF override	0
-------------------	---

Supply failure reserve	5 years
With cyclic program	Yes
With holidays program	No
With random program	No
Use	
Cycle	weekly
Safety	
Key	with programming key
Use conditions	
Operating temperature	-10...55 °C
Working accuracy	1,5
Storage/transport temperature	-20...60 °C