



EVN004



IP20

## Remote Control Dimmer universal 500W

### Technical characteristics

#### Architecture

Type of order Push button

#### Configuration

Number of modules 2

#### Main electrical features

Rated operational voltage  $U_e$  230 V

Frequency 50/60 Hz

#### Voltage

DC control voltage 24 / 110 V DC

Command voltage AC 24 / 230 V AC

Operating voltage 230 V~ +10%/-15%

#### Fuse

Fuse with electronic short-circuit and overload protection

#### Dimensions

Depth of installed product 62 mm

Height of installed product 85 mm

Installation height 0 / 1000 m

Width of installed product 35 mm

#### Length

Max distance to switches 50 mm

#### Power

Dimmable conventional transformers 500 VA

Halogen switching capacity 230V 500 W

Power consumed 4.5 W

Power consumption (operation) 4.5 W

Power consumption (standby) 0.2 W

Incandescent bulb power 500 W

Total power loss under IN 0.2 W

Conventional transformers 500 VA

Electronic transformers 500 W

#### Cover, door

Surface cover Other

**Materials**

Surface appearance	matt
--------------------	------

**Fluorescent bulbs control**

Dimmable energy-saving lamps	100 W
------------------------------	-------

Lighting power fluocompact lamps with built-in ballast	100 W
--	-------

**LED control**

Quantity of dimmable, 230 V retrofit LED lamps	10
--	----

Max number of LED/CFL lamps	10
-----------------------------	----

Dimmable 230 V LED lamps	100 W
--------------------------	-------

Power LED	100 W
-----------	-------

LED	with button and RGB LED to teach-in of the connected load
-----	---

**Incandescent bulbs control**

Max. power with incandescent lamps	500 W
------------------------------------	-------

230 V incandescent lamps and halogen lamps	500 W
--	-------

**Installation, mounting**

Fixing type	With claws
-------------	------------

Mounting type	din-Rail
---------------	----------

Installation mode	for mounting on DIN rail
-------------------	--------------------------

**Connection**

Connection cross-sect. flexible conductor	1 / 6mm <sup>2</sup>
---	----------------------

Connection cross-sect. rigid cable	1 / 6mm <sup>2</sup>
------------------------------------	----------------------

Type of load	universal
--------------	-----------

Conductor cross-section (flexible)	1.5...6 mm <sup>2</sup>
------------------------------------	-------------------------

Conductor cross-section (rigid)	1.5...6 mm <sup>2</sup>
---------------------------------	-------------------------

Type of connection	with screw terminals
--------------------	----------------------

Connection	Connection for illuminated (max. 5 mA) or standard push-buttons
------------	---

Type of connection	with screw
--------------------	------------

**Cable**

Load cable length	50 m
-------------------	------

**Settings**

Setting	setting of comfort functions (1...4) via adjusting wheel ; Reset of settings for special functions
---------	--

**Equipment**

Type of dimmer	No
----------------	----

Brightness	switch-on brightness memory function
------------	--------------------------------------

**Safety**

REACH conform	No
---------------	----

RoHS conform	Yes
--------------	-----

Halogen free	No
--------------	----

**Use conditions**

---

Operating temperature	-20...50 °C
Storage/transport temperature	-20...50 °C

**Instructions**

---

Information text Only for use with dimmable lamps!