




EE702



IP55

Compact twilight switch enhanced 16A

Technical characteristics

Architecture

Fixing mode surface-mounting

Main electrical features

Rated operational voltage U_e 230 V

Frequency 50/60 Hz

Voltage

Operating voltage 230 V~ +10%/-15%

Electric current

Acceptable current rating with AC1 16 A

Dimensions

Depth of installed product 42.5 mm

Height of installed product 95 mm

Length 80 mm

Width of installed product 42.5 mm

Power

Conventional transformers 1500 VA

Electronic transformers 1500 W

Power supply

Supply voltage 230 V

Materials

RAL colour RAL 9010 - Pure white

Lighting control

Brightness measurement range 2 / 1000 Lux

Fluorescent lamps with electronical ballast (EB) 16 x 58 W

Fluorescent bulbs control

Compact fluorescent lamps 20 x 20 W

Fluorescent lamps uncompensated 2000 W

Incandescent bulbs control

Max. power with incandescent lamps 2300 W

230 V incandescent lamps and halogen lamps 2300 W

Installation, mounting

Mounting type	surface-mounted
Installation mode	with pipe clamp for mast fixing

Connection

Connection cross-sect. flexible conductor	1 / 4mm ²
Connection cross-sect. rigid cable	1 / 4mm ²
Conductor cross-section	1...4 mm ²
Number of contacts	1
Type of contacts	1NO
Type of connection	with screw terminals

Settings

Delay ON	10 s
Delay OFF	40 s

Safety

Protection index IP	IP55
---------------------	------

Use conditions

Storage/transport temperature	-30...60 °C
-------------------------------	-------------