



EVN011



IP20

Remote Control Dimmer universal 300W

Technical characteristics

Architecture

Type of order	Push button
Fixing mode	Din-Rail

Configuration

Number of modules	1
-------------------	---

Main electrical features

Rated operational voltage Ue	230 V
Frequency	50/60 Hz

Voltage

Operating voltage	230 V~ +10%/-15%
-------------------	------------------

Fuse

Fuse	with electronic short-circuit and overload protection
------	---

Dimensions

Depth of installed product	65 mm
Height of installed product	90 mm
Installation height	0 / 1000 m
Width of installed product	17.5 mm
Width of rail mounted device (RMD)	1 modules

Length

Max distance to switches	50 mm
--------------------------	-------

Power

Dimmable conventional transformers	300 VA
Halogen switching capacity 230V	300 W
Power consumed	2.1 W
Power consumption (operation)	2.1 W
Incandescent bulb power	300 W
Total power loss under IN	0.2 W
Conventional transformers	300 VA
Electronic transformers	300 W

Cover, door

Surface cover	Other
---------------	-------

Materials

Surface appearance	matt
--------------------	------

Fluorescent bulbs control

Dimmable energy-saving lamps	60 W
Lighting power fluocompact lamps with built-in ballast	60 W

LED control

Quantity of dimmable, 230 V retrofit LED lamps	8
Max number of LED/CFL lamps	8
Dimmable 230 V LED lamps	60 W
Power LED	60 W

Incandescent bulbs control

Max. power with incandescent lamps	300 W
230 V incandescent lamps and halogen lamps	300 W

Installation, mounting

Fixing type	With claws
Mounting type	din-Rail
Installation mode	for mounting on DIN rail

Connection

Connection cross-sect. flexible conductor	1,5 / 6mm ²
Connection cross-sect. rigid cable	1,5 / 6mm ²
Type of load	universal
Conductor cross-section (flexible)	1.5...6 mm ²
Conductor cross-section (rigid)	1.5...6 mm ²
Type of connection	with screw terminals
Type of connection	with screw

Cable

Load cable length	50 m
-------------------	------

Equipment

Type of dimmer	No
Dimming principle	automatic load detection

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-10...45 °C
Storage/transport temperature	-25...70 °C

Instructions

Information text	Only for use with dimmable lamps!
------------------	-----------------------------------