



Presence detector 360°, 1 channel, wall mounted, white

Technical characteristics

Architecture

Fixing mode surface-mounting

Main electrical features

Rated operational voltage Ue 230 V

Frequency 50 Hz

Dimensions

Height of installed product 31 mm

Width of installed product 100 mm

Recommended installation height 2.5...3.5 m

Power supply

Supply voltage 230 V

Detection

Detection angle 360 °

Detection angle 360 °

Detection field Ø, at desk height ≈ 5 m

Frontal detecting distance 7 m

Side detecting distance 13 m

Materials

Colour pure white

RAL colour RAL 9010 - Pure white

Material plastic

Lighting control

Response brightness, adjustable ≈ 5...1200 lx

Brightness measurement range 5 / 1200 Lux

Installation, mounting

Maximum Mounting Height 4 m

Settings

Response value sensitivity adjustable Yes

Delay time, adjustable ≈ 1...30 mn

Equipment

Angle of horizontal detection 360 °

Safety

Protection class	isol.class II
------------------	---------------

Use conditions

Operating temperature	0...45 °C
-----------------------	-----------

Storage/transport temperature	-10...60 °C
-------------------------------	-------------

Identification

Application, usage	Motion detector
--------------------	-----------------

Main design line	Motion detectors
------------------	------------------