



EE816

IP41

Presence detector 360° monobloc DALI/DSI, flush mounted

Technical characteristics

Architecture

Bus system Without

Functions

Function can only be used as individual unit

Compatibility

Extension unit on push-button (NO), extension units can be switched on and off by retriggering

Connectivity

Outputs integrated DALI/DSI output (broadcast) for switching/controlling 24 DALI/DSI electronic ballasts

Main electrical features

Frequency 50/60 Hz

Dimensions

Dimensions (Ø x H) 78 x 70 mm

Installation opening Ø 60...63 mm

Recommended installation height 2.5...3.5 m

Installation wall thickness 10...28 mm

Power supply

Supply voltage 230 V +10% / -15%

Detection

Detection angle 360 °

Detection angle 360 °

Detection field Ø, on floor ≈ 7 m

Detection field Ø, at desk height ≈ 5 m

Frontal detecting distance 7 m

Side detecting distance 6 m

Materials

Colour white

Material plastic

Lighting control

Response brightness, adjustable ≈ 5...1000 lx

Brightness measurement range 5 / 1000 Lux

LED control

LED	with red and green acknowledge/receive LED
-----	--

Installation, mounting

Maximum Mounting Height	4 m
Installation mode	with spring clips for ceiling installation

Connection

Type of load	24 DALI/ DSI ballasts
Conductor cross-section (flexible)	0.5...1.5 mm ²
Conductor cross-section (rigid)	0.5...1.5 mm ²
Type of connection	with screw terminals

Settings

Response value sensitivity adjustable	No
Delay time, adjustable	1 mn...1 h
Setting	with potentiometers for setting the response brightness and delay time without dismantling

Equipment

Remote controllable	EE807, EE808
Angle of horizontal detection	360 °

Use conditions

Operating temperature	-10...45 °C
Energy-saving	energy saving by means of presence and brightness-dependent ON and OFF switching of light

Identification

Application, usage	Motion detector
Main design line	Motion detectors