




EE820



IP55

Motion detector Infrared 140°, IP55, wall mounted, white

Technical characteristics

Architecture

Bus system	Without
Fixing mode	surface-mounting

Functions

Function	can only be used as individual unit
----------	-------------------------------------

Main electrical features

Rated operational voltage Ue	230 V
Frequency	50/60 Hz

Dimensions

Height of installed product	2.5 m
Recommended installation height	2.5 m

Power supply

Supply voltage	230 V +10% / -15%
----------------	-------------------

Detection

Detection angle	140 °
Frontal detecting distance	16 m
Side detecting distance	8 m

Materials

Colour	white
RAL colour	RAL 9010 - Pure white
Material	plastic

Lighting control

Response brightness, adjustable	≈ 5...1000 lx
Brightness measurement range	5 / 1000 Lux

LED control

LED	with LED detection and mode indicator
-----	---------------------------------------

Installation, mounting

Maximum Mounting Height	4 m
Installation mode	for wall and ceiling mounting, corner installation with adapter

Connection

Type of connection	with plug-in terminals
--------------------	------------------------

Settings

Response value sensitivity adjustable	No
---------------------------------------	----

Delay time, adjustable	5 s...15 mn
------------------------	-------------

Setting	with potentiometers for setting the response brightness and delay time without dismantling
---------	--

Scope of delivery

Component	with fitting material
-----------	-----------------------

Equipment

Angle of horizontal detection	140 °
-------------------------------	-------

Slewing	horizontally rotatable
---------	------------------------

Safety

Protection index IP	IP55
---------------------	------

Use conditions

Operating temperature	-20...55 °C
-----------------------	-------------

Energy-saving	low intrinsic energy requirement ; energy saving by means of presence and brightness-dependent ON and OFF switching of light
---------------	--