




G4703



Input connector, 3 poles

Technical characteristics

Architecture

Number of poles	3 P
-----------------	-----

Main electrical features

Nominal voltage	230 V
-----------------	-------

Voltage

Rated surge voltage	4 kV
---------------------	------

Electric current

Rated current	25 A
---------------	------

Dimensions

Length	76 mm
--------	-------

Height	15 mm
--------	-------

Width	34.6 mm
-------	---------

Power

Fire load	0.117 kWh
-----------	-----------

Resistance

Continuity resistor	1 mΩ
---------------------	------

Cover, door

Interlockable	No
---------------	----

Materials

Colour	black
--------	-------

Colour coding / contact insert	black
--------------------------------	-------

Material	Polyamid (PA)
----------	---------------

Material group	mixed material
----------------	----------------

Connection

Connection cross section (solid-core)	0.5 ; 4 mm ²
---------------------------------------	-------------------------

Connection cross section (fine-strand)	0.5 ; 4 mm ²
--	-------------------------

Type of connection	with spring-loaded connection
--------------------	-------------------------------

Cable

Cable diameter	11 mm
----------------	-------

Equipment

Contact Material	Copper
------------------	--------

Mechanical coding

Yes

Standards

European directive RoHS

voluntary compliance

Safety

Degree of contamination

3

REACH conform

Yes

RoHS conform

Yes

Locking mechanism

None