




EE840



## Motion detector 360° white

### Technical characteristics

#### Architecture

Bus system Without

#### Functions

Function can be used as a single unit, main device or extension unit

#### Dimensions

Height of installed product 2.5 m

Recommended installation height 2.5 m

#### Measurement

Detection Method Passive Infrared

#### Power supply

Supply voltage 230 V +10% / -15%

#### Detection

Detection angle 360 °

Detection angle 360 °

Detection field Ø, on floor ≈ 12 m

Frontal detecting distance 12 m

Side detecting distance 6 m

#### Materials

Colour white

RAL colour RAL 9010 - Pure white

Material plastic

#### Lighting control

Response brightness, adjustable ≈ 5...1000 lx

Brightness measurement range 5 / 1000 Lux

#### LED control

230V LED lamps 20 x 20 W

LED with LED detection and mode indicator

#### Installation, mounting

Maximum Mounting Height 2.5 m

Installation mode for wall and ceiling mounting, corner installation with adapter

**Connection**

---

Type of connection	with screw terminals
--------------------	----------------------

---

**Settings**

---

Response value sensitivity adjustable	Yes
---------------------------------------	-----

---

Response sensitivity, settable	20...100 %
--------------------------------	------------

---

Delay time, adjustable	5 s...15 mn
------------------------	-------------

---

Setting	with potentiometers for fine adjustment of the response brightness, sensitivity and delay time
---------	--

**Scope of delivery**

---

Component	with fitting material
-----------	-----------------------

---

**Equipment**

---

Angle of horizontal detection	360 °
-------------------------------	-------

---

Slewing	vertically slewing
---------	--------------------

**Safety**

---

REACH conform	Yes
---------------	-----

---

RoHS conform	Yes
--------------	-----

**Use conditions**

---

Operating temperature	-20...55 °C
-----------------------	-------------

---

Energy-saving	low intrinsic energy requirement ; energy saving by means of presence and brightness-dependent ON and OFF switching of light
---------------	--