



EH210



IP20

## 2 modules daily time switch without reserve with clock hands

### Technical characteristics

#### Architecture

Fixing mode	Din-Rail
-------------	----------

#### Functions

Number of function channels	1
Switching cycles	min. 50000

#### Configuration

Switch mode	change-over contact, usable as NC or NO
Number of modules	2

#### Main electrical features

Frequency	50/60 Hz
-----------	----------

#### Voltage

Operating voltage	230 V~
-------------------	--------

#### Electric current

Max. power with cos phi 0.6	3 A
Switching current at cos $\varphi$ = 0.6	max. 3 A

#### Dimensions

Depth of installed product	58 mm
Height of installed product	90 mm
Width of installed product	36 mm
Width of rail mounted device (RMD)	2 modules

#### Power

Power consumed	0.5 VA
Power consumption (operation)	0.5 VA
Total power loss under IN	1 W
Loss power at full load	≈ 1 W
Power dissipation per coil	0.5 W

#### Incandescent bulbs control

Max. power with incandescent lamps	1000 W
230 V incandescent lamps and halogen lamps	max. 1000 W

#### Installation, mounting

Mounting type	din-Rail
---------------	----------

**Connection**

Connection cross-sect. flexible conductor	1 / 4mm <sup>2</sup>
Connection cross-sect. rigid cable	1 / 4mm <sup>2</sup>
Conductor cross-section (flexible)	1...4 mm <sup>2</sup>
Conductor cross-section (rigid)	1...4 mm <sup>2</sup>
Number of contacts	1
Type of contacts	1 changeover
Type of connection	with screw terminals

**Settings**

Number of program steps	96
Summer / Winter time change	manual
Shortest switching time	30 mn
Type of programming	analog
Program cycles	Programme cycle: 24 hours
Programming cycle	24H

**Equipment**

Number of channels	1
Number of switching times for on/off	96
Supply failure reserve	without
Switching cycles at $\cos \varphi = 0,6$	min. 20000

**Use**

Cycle	daily
-------	-------

**Safety**

Protection index IP	IP20
---------------------	------

**Use conditions**

Operating temperature	-10...55 °C
Working accuracy	6 mn / year
Storage/transport temperature	-20...70 °C