



EHN010

## Daily time switch 1 channel, 1 module

### Technical characteristics

#### Functions

Number of function channels	1
Switching cycles	min. 50000
Slide switch	with slide switch for permanent on/automatic

#### Configuration

Switch mode	NO contact
Number of modules	1

#### Main electrical features

Frequency	50/60 Hz
-----------	----------

#### Voltage

Operating voltage	230 V~
-------------------	--------

#### Electric current

Max. power with $\cos \phi$ 0.6	3 A
Switching current at $\cos \phi = 0.6$	max. 3 A

#### Dimensions

Depth of installed product	60 mm
Height of installed product	90 mm
Width of installed product	18 mm
Width of rail mounted device (RMD)	1 modules

#### Power

Power consumed	0.5 VA
Power consumption (operation)	0.5 VA
Total power loss under IN	1 W
Loss power at full load	≈ 1 W
Power dissipation per coil	0.5 W

#### Fluorescent bulbs control

Compact fluorescent lamps	max. 100 W
---------------------------	------------

#### Incandescent bulbs control

Max. power with incandescent lamps	900 W
230 V incandescent lamps and halogen lamps	max. 900 W

#### Installation, mounting

Mounting type	din-Rail
Installation mode	for mounting on DIN rail
<b>Connection</b>	
Connection cross-sect. flexible conductor	1 / 4mm <sup>2</sup>
Connection cross-sect. rigid cable	1 / 4mm <sup>2</sup>
Conductor cross-section (flexible)	1...4 mm <sup>2</sup>
Conductor cross-section (rigid)	1...4 mm <sup>2</sup>
Number of contacts	1
Type of contacts	1 changeover
Type of connection	with screw terminals
Contact	with potential-free switching contact
Type of connection	with screw
<b>Settings</b>	
Number of program steps	96
Summer / Winter time change	manual
Shortest switching time	15 mn
Type of programming	analog
Program cycles	Programme cycle: 24 hours
Programming cycle	24H
Setting	Setting via day dial
<b>Equipment</b>	
Number of channels	1
Number of switching times for on/off	96
Supply failure reserve	without
Switching cycles at $\cos \varphi = 0,6$	min. 20000
<b>Use</b>	
Cycle	daily
<b>Safety</b>	
REACH conform	Yes
RoHS conform	Yes
Halogen free	No
<b>Use conditions</b>	
Operating temperature	-10...55 °C
Working accuracy	1
Storage/transport temperature	-20...70 °C