



HA453M

Load break switch 4P 200A

Technical characteristics

Architecture

Type of order	Long thumb-grip
Number of poles	4 P
Type of pole	4 P
Type of case	Fixed built-in

Functions

Reversing switch	No
------------------	----

Configuration

Number of modules	12
-------------------	----

Controls and indicators

Motor drive integrated	No
------------------------	----

Main electrical features

Rated operational voltage Ue	380 / 415 V
------------------------------	-------------

Voltage

Rated insulation voltage	800 V
Rated impulse withstand voltage	8000 V

Electric current

Rated operational current in AC21 category B	200 A
Acceptable current rating with AC22 category A	200 A
Rated current	200 A
Short-circuit current with gI-gG fuses	50 kA
Rated short-time withstand current 1s	7 kA
Thermal rated current outside of housings	200 A
Rated operational current in AC21 category A	200 A
Acceptable current rating with AC22 category B	200 A
Rated operational current in AC23 category A	200 A
Acceptable current rating with AC23 category B	200 A
Conventional thermal current under enclosure at 40°C	200 A

Power

Total power loss under IN	19.2 W
Power loss per pole at In	4.8 W
Contact rating with 400 V in AC1	131 kW
Cover, door	
Interlockable	Yes
Installation, mounting	
Tightening torque	9 - 9.9 Nm
Fixation type	Back plate mounting
Connection	
Connection cross-sect. rigid cable	95mm ²
Type of connection	Terminal
Equipment	
Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0
Width available for insulation connection	95 mm ²
Motor drive optional	No
Safety	
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
Use conditions	
Operating temperature	-20...70 °C