




EN145



Interface relay VLV/ LV

Technical characteristics

Configuration

Number of modules	1
-------------------	---

Main electrical features

Rated operational voltage Ue	250 V
Frequency	50/60 Hz

Voltage

Rated insulation voltage	250 V
DC control voltage	10 / 26 V
Command voltage AC	10 / 26 V
Type of voltage input 1	DC

Electric current

Acceptable current rating with AC1	5 A
Max. power with cos phi 0.6	5 A
Rated current	5 A

Dimensions

Depth of installed product	58 mm
Height of installed product	85 mm
Width of installed product	17.5 mm

Power

Inrush power absorbed	2 VA
Operating consumption	2 VA
Total power loss under IN	2 W

Connection

Connection cross-sect. flexible conductor	0,5 / 4mm ²
Connection cross-sect. rigid cable	1 / 6mm ²
Number of contacts	1
Type of contacts	1 changeover
Type of connection	with screw
Connection cross-section of the control cable solid	1 / 6 mm ²

Equipment

Quantity of NC contacts	0
Quantity of NO contacts	0
Quantity of INV contacts	1

Safety

RoHS conform

Yes

Use conditions

Operating temperature

-10...50 °C

Storage/transport temperature

-40...80 °C