



EPN503



## Latching relay 1NO+1NC 48V

### Technical characteristics

#### Functions

Max. temporisation	60 s
--------------------	------

#### Configuration

Number of modules	1
-------------------	---

#### Main electrical features

Rated operational voltage Ue	250 V
------------------------------	-------

#### Voltage

Rated insulation voltage	250 V
--------------------------	-------

DC control voltage	24 V
--------------------	------

Command voltage AC	48 V
--------------------	------

#### Electric current

Quiescent current	6 mA
-------------------	------

Rated current	16 A
---------------	------

#### Dimensions

Depth of installed product	63 mm
----------------------------	-------

Height of installed product	83 mm
-----------------------------	-------

Width of installed product	17.5 mm
----------------------------	---------

#### Frequency

Frequency	50 to 60 Hz
-----------	-------------

#### Power

Inrush power absorbed	25 VA
-----------------------	-------

Total power loss under IN	1.2 W
---------------------------	-------

#### Resistance

Winding resistance	48 Ω
--------------------	------

#### Endurance

Electrical durability at nominal load in AC21in operating cycles	150000
--	--------

Number of mechanical operations	500000
---------------------------------	--------

#### Fluorescent bulbs control

Max. power with fluorescent parallel lamps	900 VA
--	--------

#### Incandescent bulbs control

Max. power with incandescent lamps

1800 W

---

### Installation, mounting

---

Tightening torque	1,6Nm
-------------------	-------

---

### Connection

---

Connection cross-sect. flexible conductor	1 / 6mm <sup>2</sup>
---	----------------------

---

Connection cross-sect. rigid cable	1,5 / 10mm <sup>2</sup>
------------------------------------	-------------------------

---

Number of contacts	2
--------------------	---

---

Type of contacts	1NC+1NO
------------------	---------

---

### Equipment

---

Type of latching relay	electromechanic
------------------------	-----------------

---

### Use

---

Pulse duration	50 ms
----------------	-------

---

### Standards

---

Standard text	IEC/EN 60669-2
---------------	----------------

---

European directive WEEE	concerned
-------------------------	-----------

---

### Safety

---

REACH conform	Yes
---------------	-----

---

RoHS conform	Yes
--------------	-----

---

Halogen free	No
--------------	----

---

### Use conditions

---

Operating temperature	-5...40 °C
-----------------------	------------

---

Storage/transport temperature	-40...80 °C
-------------------------------	-------------

---

Manual operation possible	Yes
---------------------------	-----