



HA453M

## Load break switch 4P 200A

### Technical characteristics

#### Architecture

Number of poles	4 P
Type of pole	4 P
Type of case	Fixed built-in

#### Functions

Reversing switch	No
------------------	----

#### Configuration

Number of modules	12
-------------------	----

#### Controls and indicators

Motor drive integrated	No
------------------------	----

#### Main electrical features

Rated operational voltage Ue	380 / 415 V
------------------------------	-------------

#### Voltage

Rated insulation voltage	800 V
Rated impulse withstand voltage	8000 V

#### Electric current

Rated operational current in AC21category B	200 A
Acceptable current rating with AC22 category A	200 A
Rated current	200 A
Short-circuit current with gI-gG fuses	50 kA
Rated short-time withstand current 1s	7 kA
Thermal rated current outside of housings	200 A
Rated operational current in AC21 category A	200 A
Acceptable current rating with AC22 category B	200 A
Rated operational current in AC23 category A	200 A
Acceptable current rating with AC23 category B	200 A
Conventional thermal current under enclosure at 40°C	200 A

#### Power

Total power loss under IN	19.2 W
---------------------------	--------

Power loss per pole at In	4.8 W
Contact rating with 400 V in AC1	131 kW
<b>Cover, door</b>	
Interlockable	Yes
<b>Installation, mounting</b>	
Fixation type	Back plate mounting
<b>Connection</b>	
Type of connection	Terminal
<b>Equipment</b>	
Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0
Width available for insulation connection	95 mm <sup>2</sup>
Motor drive optional	No
<b>Standards</b>	
European directive WEEE	concerned
<b>Safety</b>	
Protection index IP	IP00
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes
<b>Use conditions</b>	
Operating temperature	-20...70 °C