



HAB306

## Load break switch 3P 63A

### Technical characteristics

#### Architecture

Number of poles	3 P
Type of pole	3 P
Type of case	Fixed built-in

#### Functions

Reversing switch	No
------------------	----

#### Configuration

Number of modules	2.57
-------------------	------

#### Controls and indicators

Motor drive integrated	No
------------------------	----

#### Main electrical features

Rated operational voltage U <sub>e</sub>	380 / 415 V
Frequency	50 Hz

#### Voltage

Rated insulation voltage	800 V
Rated impulse withstand voltage	8000 V

#### Electric current

Rated operational current in AC21 category B	63 A
Acceptable current rating with AC22 category A	63 A
Rated current	63 A
Short-circuit current with gI-gG fuses	50 kA
Rated short-time withstand current 1s	1.26 kA
Rated operational current in AC21 category A	63 A
Acceptable current rating with AC22 category B	63 A
Rated operational current in AC23 category A	40 A
Acceptable current rating with AC23 category B	40 A

#### Power

Total power loss under I <sub>N</sub>	7.2 W
Power loss per pole at I <sub>N</sub>	2.4 W
Contact rating with 400 V in AC1	41 kW

<b>Cover, door</b>	
Interlockable	Yes
<b>Connection</b>	
Connection cross-sect. rigid cable	16mm <sup>2</sup>
<b>Equipment</b>	
Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0
Motor drive optional	No
<b>Standards</b>	
Standard text	IEC 60947-3
European directive WEEE	concerned
<b>Safety</b>	
Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes
Halogen free	No
<b>Use conditions</b>	
Operating temperature	-20...70 °C