



EVN012



IP20

Universal Remote Control Dimmers 300W Comfort

Technical characteristics

Architecture

Type of order Push button

Functions

Slide switch Comfort functions (1-4) switchable via selection switch

Configuration

Number of modules 1

Controls and indicators

Button / push-button with configuration button for teach-in of load and RGB status LED

Main electrical features

Rated operational voltage U_e 230 V

Frequency 50/60 Hz

Voltage

Operating voltage 230 V~ +10%/-15%

Fuse

Fuse with electronic short-circuit and overload protection

Dimensions

Depth of installed product 65 mm

Height of installed product 90 mm

Installation height 0 / 1000 m

Width of installed product 17.5 mm

Width of rail mounted device (RMD) 1 modules

Length

Max distance to switches 50 mm

Power

Dimmable conventional transformers 300 VA

Halogen switching capacity 230V 300 W

Power consumed 2.1 W

Power consumption (operation) 2.1 W

Incandescent bulb power 300 W

Total power loss under IN 0.2 W

Conventional transformers 300 VA

Cover, door

Surface cover	Other
---------------	-------

Materials

Surface appearance	matt
--------------------	------

Fluorescent bulbs control

Dimmable energy-saving lamps	60 W
------------------------------	------

Lighting power fluocompact lamps with built-in ballast	60 W
--	------

LED control

Quantity of dimmable, 230 V retrofit LED lamps	8
--	---

Max number of LED/CFL lamps	8
-----------------------------	---

Dimmable 230 V LED lamps	60 W
--------------------------	------

Power LED	60 W
-----------	------

Incandescent bulbs control

Max. power with incandescent lamps	300 W
------------------------------------	-------

230 V incandescent lamps and halogen lamps	300 W
--	-------

Installation, mounting

Fixing type	With claws
-------------	------------

Mounting type	din-Rail
---------------	----------

Installation mode	for mounting on DIN rail
-------------------	--------------------------

Connection

Connection cross-sect. flexible conductor	1,5 / 6mm ²
---	------------------------

Connection cross-sect. rigid cable	1,5 / 6mm ²
------------------------------------	------------------------

Type of load	universal
--------------	-----------

Conductor cross-section (flexible)	1.5...6 mm ²
------------------------------------	-------------------------

Conductor cross-section (rigid)	1.5...6 mm ²
---------------------------------	-------------------------

Type of connection	with screw terminals
--------------------	----------------------

Connection	Connection for illuminated (max. 5 mA) or standard push-buttons
------------	---

Type of connection	with screw
--------------------	------------

Cable

Load cable length	50 m
-------------------	------

Equipment

Type of dimmer	No
----------------	----

Dimming principle	automatic load detection
-------------------	--------------------------

Safety

REACH conform	No
---------------	----

RoHS conform	Yes
--------------	-----

Halogen free	No
--------------	----

Use conditions

Operating temperature

-10...45 °C

Storage/transport temperature

-25...70 °C

Instructions

Information text

Only for use with dimmable lamps!