



HBB161H

Electronic earth leakage add-on block 4P 160A I_{dn} adjustable, time delay

Technical characteristics

Architecture

Neutral position	not applicable
Number of poles	4 P
Fixing mode	DIN rail type O (symmetrical)

Main electrical features

Rated operational voltage U _e	220 / 415 V
--	-------------

Voltage

Rated insulation voltage	500 V
Rated impulse withstand voltage	6 kV

Electric current

Rated residual operating current	30 mA / 100 mA / 300 mA / 1 A / 3 A / 6 A
Rated current	160 A
Withstand not tripping on 8-20 μs wave	5 kA

Frequency

Frequency	50 to 60 Hz
-----------	-------------

Tripping

Protected against nuisance tripping	Yes
-------------------------------------	-----

Connection

Connection cross-section at output with screw, for flexible conductor	35 / 150 mm ²
Connection cross-section at output with screw, for massive conductor	35 / 185 mm ²
Connection cross-section of input and output with screws, for massive conductors	35 / 185 mm ²
Connection cross section of access and exit with screws, for flexible conductor	35 / 150 mm ²

Settings

Rated fault current adjustable	Yes
Delay adjustable	Yes
Time delay of residual current	0 / 0.06 / 0.15 / 0.3 / 0.5 / 1 s

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP4X
---------------------	------

Residual current type	A HI
REACH conform	No
RoHS conform	Yes
Halogen free	No
Use conditions	
Degree of pollution according to IEC 60664 / IEC 60947-2	3
Altitude	2000 m