



FWB74S

**FWB encl.,univers,7-rows 336 modules cl.II IP44 w.plain door, 1100x1050x161mm,QC**

**Technical characteristics**

**Functions**

With a pipe-in lead	Yes
Protection main switch	No

**Configuration**

Module	with terminals
Number of modules	336

**Compatibility**

Suitable for Multimedia	No
-------------------------	----

**Electric current**

Rated current	125 A
---------------	-------

**Dimensions**

Depth of installed product	165 mm
Internal depth	156 mm
Height of installed product	1100 mm
Installation height	1100 mm
Width of installed product	1050 mm
Width in division units	48
Thickness of sidewall material	1 mm

**Cover, door**

Type of door closing	Hinged pattern handle and bar locking
Number of keylock of the door	1
Cover type	With Notch
Door locking	without
Door leave	single
Cover type	Door
Transparent cover or door	No

**Materials**

Copper weight of the product	0.162 kg
Colour	white
RAL colour	RAL 9010 - Pure white
Material	sheet steel

**Installation, mounting**

Suitable for outdoor use	No
--------------------------	----

**Connection**

Number of conduit inlets	16
--------------------------	----

**Settings**

Enclosure type	Field distributor surface mounted
----------------	-----------------------------------

**Equipment**

Number of rows	7
----------------	---

Quantity of section in width	4
------------------------------	---

Number of keys	1
----------------	---

Quantity of rails	28
-------------------	----

Can be accessorized	Yes
---------------------	-----

Number of openings for flange plates	8
--------------------------------------	---

Extension possible	Yes
--------------------	-----

Earthing terminal block	Yes
-------------------------	-----

Neutral terminal block	Yes
------------------------	-----

Signal passing door	No
---------------------	----

**Standards**

GWT Glow wire test	750 °C
--------------------	--------

Protection class according to IEC-61140	II
---	----

**Safety**

IK protection code against mechanical impacts	09
---	----

Protection index IP	IP44
---------------------	------

Protection class	isol.class II
------------------	---------------

REACH conform	No
---------------	----

RoHS conform	Yes
--------------	-----

Halogen free	No
--------------	----

Impact strength	IK09
-----------------	------