



HCD400H

## Switch h630 3P 400A

### Technical characteristics

#### Architecture

Type of order	Toggle
Neutral position	without neutral
Number of poles	3 P
Type of pole	3 P

#### Functions

Reversing switch	No
Trip Unit	SWITCH

#### Main electrical features

Rated operational voltage Ue	220 / 690 V
Frequency	50/60 Hz

#### Voltage

Rated insulation voltage	800 V
Rated impulse withstand voltage	8 kV

#### Electric current

Rated current	400 A
Rated operational current in AC21	400 A

#### Current correction factors

Correction factor of rating current for 2 devices placed side-by-side	1
Correction factor of rating current for 3 devices placed side-by-side	1
Correction factor of rating current for 4 and 5 devices placed side-by-side	1
Correction factor of rating current for 6 devices placed side-by-side	1

#### Power

Total power loss under I <sub>N</sub>	62.4 W
Power loss per pole at I <sub>N</sub>	20.8 W
Contact rating with 400 V in AC1	263 kW

#### Tripping

Time of response when opening	10 ms
-------------------------------	-------

#### Endurance

Electric endurance in number of cycles	4500
--	------

**Cover, door**

Interlockable	Yes
---------------	-----

**Materials**

Toggle colour	Black
---------------	-------

**Connection**

Connection cross-sect. flexible conductor	35 / 240mm <sup>2</sup>
Connection cross-sect. rigid cable	35 / 240mm <sup>2</sup>
Connection	Front connection
Type of connection	Terminal

**Equipment**

Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0
Motor drive optional	Yes

**Use cases**

Category of use	A
-----------------	---

**Standards**

Standard text	IEC 60947-3
---------------	-------------

**Use conditions**

Operating temperature	-25...70 °C
Degree of pollution according to IEC 60664 / IEC 60947-2	3
Altitude	2000 m
Air humidity protection	85% / 50°C
Storage/transport temperature	-35...70 °C