




G4703



Input connector, 3 poles

Technical characteristics

Architecture

Number of poles	3 P
Type of pole	L PE N

Configuration

Module	Buchse (Jack)
--------	---------------

Main electrical features

Nominal voltage	230 V
-----------------	-------

Voltage

Rated surge voltage	4 kV
---------------------	------

Electric current

Rated current	25 A
---------------	------

Dimensions

Length	76 mm
Height	15 mm
Width	34.6 mm

Power

Fire load	0.117 kWh
-----------	-----------

Resistance

Continuity resistor	1 mΩ
---------------------	------

Cover, door

Interlockable	No
---------------	----

Materials

Colour	black
Colour coding / contact insert	black
Material group	mixed material

Connection

Connection cross section (solid-core)	0.5 ; 4 mm ²
Connection cross section (fine-strand)	0.5 ; 4 mm ²
Type of connection	with spring-loaded connection

Cable

Cable diameter	11 mm
----------------	-------

Equipment

Contact Material	Copper
Mechanical coding	Yes

Standards

European directive RoHS	voluntary compliance
-------------------------	----------------------

Safety

Degree of contamination	3
REACH conform	Yes
RoHS conform	Yes
Locking mechanism	None
