



HA354

Load break switch 3P 250A

Technical characteristics

Architecture

Type of order	Long thumb-grip
Number of poles	3 P
Type of pole	3 P
Type of case	Fixed built-in

Functions

Reversing switch	No
------------------	----

Controls and indicators

Motor drive integrated	No
------------------------	----

Main electrical features

Rated operational voltage Ue	380 / 415 V
------------------------------	-------------

Voltage

Rated insulation voltage	800 V
Rated impulse withstand voltage	8000 V

Electric current

Rated operational current in AC21category B	250 A
Acceptable current rating with AC22 category A	250 A
Cut off current	4.3 kA
Rated current	250 A
Short-circuit current with gI-gG fuses	50 kA
Rated short-time withstand current 1s	9 kA
Thermal rated current outside of housings	250 A
Rated operational current in AC21 category A	250 A
Acceptable current rating with AC22 category B	250 A
Rated operational current in AC23 category A	200 A
Acceptable current rating with AC23 category B	200 A
Conventional thermal current under enclosure at 40°C	250 A

Dimensions

Depth of installed product	130 mm
Height of installed product	160 mm

Width of installed product 180 mm

Power

Nominal power under 440/500, 50Hz	90 kW
Total power loss under IN	17.4 W
Power loss per pole at In	5.8 W
Contact rating with 400 V in AC1	164 kW

Cover, door

Interlockable	Yes
---------------	-----

Installation, mounting

Fixation type	Back plate mounting
---------------	---------------------

Connection

Connection cross-sect. flexible conductor	120mm ²
Connection cross-sect. rigid cable	150mm ²
Type of connection	Terminal

Equipment

Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0
Width available for insulation connection	185 mm ²
Motor drive optional	No

Standards

Standard text	IEC 60947-3
---------------	-------------

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

Use conditions

Operating temperature	-20...70 °C
-----------------------	-------------