



HEC250H

Moulded Case Circuit Breaker h250 3P 70kA 250A LSI

Technical characteristics

Architecture

Type of order	Toggle
Number of poles	3 P
Type of pole	3P3D

Functions

Complete device with protection unit	Yes
Trip Unit	LSI
Integrated earth fault protection	No

Configuration

Number of modules	6
-------------------	---

Main electrical features

Rated operational voltage Ue	220 / 690 V
Frequency	50/60 Hz

Voltage

Rated insulation voltage	800 V
Rated impulse withstand voltage	8 kV
With under voltage release	No

Electric current

Rated current	250 A
Rated ultimate short-circuit breaking capacity Icu under 690V AC IEC 60947-2	20 kA
Thermal protection nob setting xIN	0.4 / 0.5 / 0.63 / 0.8 / 0.9 / 0.95 / 1
Breaking capacity on 1 pole for IT 230V NF 60947-2	51 kA
Breaking capacity on 1 pole for IT 400V NF 60947-2	9 kA
Rated service breaking capacity Ics AC according IEC 60947-2	71 %
Rated ultimate short-circuit breaking capacity Icu under 230V AC IEC 60947-2	100 kA
Rated ultimate short-circuit breaking capacity Icu under 240V AC IEC 60947-2	85 kA
Rated ultimate short-circuit breaking capacity Icu under 400V AC IEC 60947-2	70 kA
Rated ultimate short-circuit breaking capacity Icu under 415V AC IEC 60947-2	70 kA
Rated ultimate short-circuit breaking capacity Icu under 440V AC IEC 60947-2	50 kA

Current correction factors

Correction factor of rating current for 2 devices placed side-by-side	1
Correction factor of rating current for 3 devices placed side-by-side	1
Correction factor of rating current for 4 and 5 devices placed side-by-side	1
Correction factor of rating current for 6 devices placed side-by-side	1

Power

Total power loss under IN	73.2 W
Power loss per pole at In	24.4 W

Tripping

Tripmode	LSI
Thermal protection trip time	5 / 8 / 11 / 21 ms
Time of response when opening	10 ms

Electrical specifications

Magnetic trip delay time	100 to 200 ms
--------------------------	---------------

Endurance

Electric endurance in number of cycles	1000
Number of mechanical operations	4000

Installation, mounting

DIN rail mounting with optional adaptor	No
---	----

Connection

Connection cross-sect. flexible conductor	35 / 150mm ²
Connection cross-sect. rigid cable	35 / 185mm ²
Connection	Front connection
Type of connection	Terminal

Settings

Range of the magnetic adjustment	1400 / 1750 / 2240 / 2800 / 3150 / 3250 / 3250 A
Magnetic protection nob setting xIN	2.5 / 5 / 10
Setting type In or Ith	IrTh

Equipment

Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0
Motor drive optional	Yes

Use cases

Category of use	A
-----------------	---

Standards

Safety

REACH conform	Yes
RoHS conform	Yes

Use conditions

Operating temperature	-25...70 °C
Altitude	2000 m
Air humidity protection	for all climates
Storage/transport temperature	-35...70 °C
