




HBW400H



## RCD add on P630 4P 400A I<sub>dn</sub> adj

### Technical characteristics

#### Architecture

Neutral position	left
Number of poles	4 P

#### Main electrical features

Rated operational voltage U <sub>e</sub>	220 / 415 V
Type of supply voltage	AC

#### Voltage

Rated insulation voltage	500 V
Rated impulse withstand voltage	6 kV

#### Electric current

Rated residual operating current	100 mA / 300 mA / 500 mA / 1 A / 3 A / 10 A
Rated current	400 A
Withstand not tripping on 8-20 µs wave	3 kA

#### Frequency

Frequency	50 to 60 Hz
-----------	-------------

#### Tripping

Protected against nuisance tripping	Yes
-------------------------------------	-----

#### Settings

Rated fault current adjustable	Yes
Delay adjustable	Yes
Time delay of residual current	0 / 100 / 300 / 500 / 1000 / 3000 ms

#### Safety

Residual current type	A
REACH conform	No
RoHS conform	Yes
Halogen free	No

#### Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2	3
Altitude	2000 m

