



HHA101Z

Moulded Case Circuit Breaker h3 x160 TM FIX 4P4D 100A 25kA CTC

Technical characteristics

Architecture

Number of protected poles	4
Number of poles	4 P
Type of case	FIX

Functions

Complete device with protection unit	Yes
Trip Unit	TM F/F
Integrated earth fault protection	No

Controls and indicators

Motor drive integrated	No
------------------------	----

Main electrical features

Rated operational voltage Ue	220 / 415 V
Frequency	50/60 Hz

Voltage

Rated insulation voltage	690 V
Rated impulse withstand voltage	8 kV
With under voltage release	No

Electric current

Rated current	100 A
Thermal protection nob setting xIN	1
Rating current 10°C according to IEC 60947	120.5 A
Rating current 15°C according to IEC 60947	118.1 A
Rating current 20°C according to IEC 60947	115.7 A
Rating current 25°C according to IEC 60947	113.2 A
Rating current 30°C according to IEC 60947	110.7 A
Rating current 35°C according to IEC 60947	108.1 A
Rating current 40°C according to IEC 60947	105.5 A
Rating current 45°C according to IEC 60947	102.7 A
Rating current 50°C according to IEC 60947	100 A
Rating current 55°C according to IEC 60947	97.1 A
Rating current 60°C according to IEC 60947	94.1 A
Rating current 65°C according to IEC 60947	91.1 A
Rating current 70°C according to IEC 60947	87.9 A
Rated ultimate short-circuit breaking capacity Icu under 230V AC IEC 60947-2	35 kA

Rated ultimate short-circuit breaking capacity Icu under 240V AC IEC 60947-2	35 kA
Rated ultimate short-circuit breaking capacity Icu under 400V AC IEC 60947-2	25 kA
Rated ultimate short-circuit breaking capacity Icu under 415V AC IEC 60947-2	25 kA
Range of the thermal adjustment	100 A
Rated ultimate short-circuit breaking capacity Icu under 380V AC IEC 60947-2	25 kA
Dimensions	
Depth of installed product	68 mm
Height of installed product	130 mm
Width of installed product	100 mm
Frequency	
Frequency	50 to 60 Hz
Power	
Total power loss under IN	39 W
Power loss per pole at In	13 W
Endurance	
Electric endurance in number of cycles	1000
Number of mechanical operations	4000
Installation, mounting	
DIN rail mounting with optional adaptor	Yes
Settings	
Range of the magnetic adjustment	1500 A
Equipment	
Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0
Motor drive optional	Yes
Can be accessorized	Yes
Standards	
Standard text	IEC 60947-2
European directive WEEE	concerned
Use conditions	
Degree of pollution according to IEC 60664 / IEC 60947-2	3
Altitude	2000 m
temperatur	
Temperature of calibration	50 °C