



HCT251AR

## Load Break Switch Disconnecter h3+ P250 4P 250A FTC

### Technical characteristics

#### Architecture

Type of order	Toggle
Neutral position	left
Number of poles	4 P
Type of pole	4 P
Fixing mode	fixing plate
Type of case	Fixed built-in

#### Functions

Reversing switch	No
Version as main switch	Yes
Version as emergency stop installation	Yes
Version as safety switch	No
Version as maintenance-/service switch	Yes
Trip Unit	SWITCH
Concurrently switching N-neutral	Yes

#### Controls and indicators

Motor drive integrated	No
------------------------	----

#### Main electrical features

Rated operational voltage Ue	220 / 690 V
Type of supply voltage	AC
Frequency	50/60 Hz

#### Voltage

Rated insulation voltage	800 V
Rated impulse withstand voltage	8 kV

#### Electric current

Rated current	250 A
Rated short-time withstand current I <sub>cw</sub>	3.6 kA
Rated short-time withstand current I <sub>cw</sub> t=1s 660-690 V AC according IEC 60947-3	3.6 kA
Rated short-time withstand current I <sub>cw</sub> t=1s 220-240 V AC according IEC 60947-3	3.6 kA
Rated short-time withstand current I <sub>cw</sub> t=1s 380-415 V AC according IEC 60947-3	3.6 kA
Rated operational current in AC21	250 A

#### Dimensions

Depth of installed product	97 mm
Height of installed product	165 mm
Width of installed product	140 mm
<b>Frequency</b>	
Frequency	50 to 60 Hz
<b>Power</b>	
Total power loss under IN	50.7 W
Power loss per pole at In	16.9 W
<b>Endurance</b>	
Electric endurance in number of cycles	10000
Number of mechanical operations	40000
<b>Cover, door</b>	
Interlockable	Yes
<b>Materials</b>	
Toggle colour	Grey
<b>Installation, mounting</b>	
Tightening torque	12Nm
DIN rail mounting with optional adaptor	No
Suitable for front mounting center	No
Suitable for front mounting	No
Suitable for ground mounting	Yes
<b>Connection</b>	
Connection cross-sect. flexible conductor	35 / 150mm <sup>2</sup>
Connection cross-sect. rigid cable	35 / 185mm <sup>2</sup>
Connection	Front connection
Type of connection	Terminal
<b>Cable</b>	
Cable Material	Cu / Al
<b>Equipment</b>	
Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0
Motor drive optional	Yes
Can be accessorized	Yes
<b>Use cases</b>	
Category of use	A
<b>Use</b>	
Vibrations and shocks withstand	IEC 68068-2-52 Test FC

**Standards**

Standard text	IEC 60947-3
European directive WEEE	concerned

**Safety**

Protection index IP	IP4X
REACH conform	Yes
RoHS conform	Yes
Halogen free	No

**Use conditions**

Degree of pollution according to IEC 60664 / IEC 60947-2	3
Altitude	2000 m
Air humidity protection	95%HR 55°C sev Kn (IEC 68-2-30/52)

**temperatur**

Temp.-rise limits for access. parts (toggle) according to product standard	25 K
Temp.-rise limits for access. parts (not touched) according to product standard	50 K
Temp.rise limits for access. parts (to be touched) according to product standard	40 K
Temperature-rise limits for terminals according to the product standard	65 K