



HHS025DC

## Moulded Case Circuit Breaker h3+ P160 TM ADJ 3P3D 25A 25kA CTC

### Technical characteristics

#### Architecture

Neutral position	without neutral
Number of protected poles	3
Number of poles	3 P
Fixing mode	fixing plate
Type of case	Fixed built-in

#### Functions

Complete device with protection unit	Yes
Reversing switch	No
Version as main switch	Yes
Version as emergency stop installation	No
Version as safety switch	No
Version as maintenance-/service switch	Yes
Trip Unit	TM A/A
Integrated earth fault protection	No

#### Controls and indicators

Motor drive integrated	No
------------------------	----

#### Main electrical features

Rated operational voltage Ue	220 / 690 V
Type of supply voltage	AC
Frequency	50/60 Hz

#### Voltage

Rated insulation voltage	800 V
Rated impulse withstand voltage	8 kV
With under voltage release	No

#### Electric current

Rated current	25 A
Rated ultimate short-circuit breaking capacity Icu under 690V AC IEC 60947-2	6 kA
Thermal protection nob setting xIN	0.63 / 0.8 / 1
Rating current 10°C according to IEC 60947	30.1 A
Rating current 15°C according to IEC 60947	29.6 A
Rating current 20°C according to IEC 60947	28.9 A
Rating current 25°C according to IEC 60947	28.3 A
Rating current 30°C according to IEC 60947	27.7 A

Rating current 35°C according to IEC 60947	27 A
Rating current 40°C according to IEC 60947	26.4 A
Rating current 45°C according to IEC 60947	25.7 A
Rating current 50°C according to IEC 60947	25 A
Rating current 55°C according to IEC 60947	24.3 A
Rating current 60°C according to IEC 60947	23.5 A
Rating current 65°C according to IEC 60947	22.8 A
Rating current 70°C according to IEC 60947	22 A
Rated service breaking capacity Ics under 660V AC according IEC 60947-2	6 kA
Breaking capacity on 1 pole for IT 230V NF 60947-2	6 kA
Breaking capacity on 1 pole for IT 400V NF 60947-2	6 kA
Breaking capacity on 1 pole for IT 415V NF 60947-2	6 kA
Breaking capacity on 1 pole for IT 690V NF 60947-2	2.5 kA
Rated ultimate short-circuit breaking capacity Icu under 230V AC IEC 60947-2	35 kA
Rated ultimate short-circuit breaking capacity Icu under 240V AC IEC 60947-2	35 kA
Rated ultimate short-circuit breaking capacity Icu under 400V AC IEC 60947-2	25 kA
Rated ultimate short-circuit breaking capacity Icu under 415V AC IEC 60947-2	25 kA
Range of the thermal adjustment	16 / 20 / 25 A
Rated service breaking capacity Ics under 110-138V AC according IEC 60947-2	35 kA
Rated ultimate short-circuit breaking capacity Icu under 220V AC IEC 60947-2	35 kA
Rated ultimate short-circuit breaking capacity Icu under 380V AC IEC 60947-2	25 kA
Rated ultimate short-circuit breaking capacity Icu under 660V AC IEC 60947-2	6 kA
<b>Dimensions</b>	
Depth of installed product	97 mm
Height of installed product	130 mm
Width of installed product	90 mm
<b>Frequency</b>	
Frequency	50 to 60 Hz
<b>Power</b>	
Power loss per pole at 0.63*In	2.66 W
Power loss per pole at 0.8*In	4.16 W
Total power loss at 0.63*In	7.99 W
Total power loss at 0.8*In	12.48 W
Total power loss under IN	19.5 W
Power loss per pole at In	6.5 W
<b>Tripping</b>	
Short-time delayed tripping	No

Subject to technical modifications

**Endurance**

Electric endurance in number of cycles	10000
Number of mechanical operations	40000

**Cover, door**

Interlockable	Yes
---------------	-----

**Installation, mounting**

Tightening torque	6Nm
DIN rail mounting with optional adaptor	Yes
Suitable for front mounting center	No
Suitable for front mounting	No
Suitable for ground mounting	Yes

**Connection**

Connection cross-sect. rigid cable	6 / 95mm <sup>2</sup>
------------------------------------	-----------------------

**Protection**

Instantaneous protection (li): type	fixed
-------------------------------------	-------

**Cable**

Cable Material	Cu
----------------	----

**Settings**

Range of the magnetic adjustment	150 / 200 / 250 / 300 A
Magnetic protection nob setting xIN	6 / 8 / 10 / 12

**Equipment**

Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0
Motor drive optional	No
Can be accessorized	Yes

**Use cases**

Category of use	A
-----------------	---

**Use**

Vibrations and shocks withstand	IEC 68068-2-52 Test FC
---------------------------------	------------------------

**Standards**

Standard text	IEC 60947-2
European directive WEEE	concerned

**Safety**

REACH conform	Yes
RoHS conform	Yes
Halogen free	No

**Use conditions**

Degree of pollution according to IEC 60664 / IEC 60947-2	3
---	---

Altitude	2000 m
----------	--------

**temperatur**

Temperature of calibration	50 °C
----------------------------	-------