



HDA030Z

Moulded Case Circuit Breaker h3 x160 TM FIX 1P1D 32A 18kA CTC

Technical characteristics

Architecture

Neutral position	without neutral
Number of protected poles	1
Number of poles	1 P
Type of pole	1P1D

Functions

Trip Unit	TM F/F
Integrated earth fault protection	No
Concurrently switching N-neutral	No

Controls and indicators

Motor drive integrated	No
------------------------	----

Main electrical features

Rated operational voltage Ue	220 / 240 V
Type of supply voltage	AC
Frequency	50/60 Hz

Voltage

Rated insulation voltage	690 V
Rated impulse withstand voltage	8 kV
With under voltage release	No

Electric current

Rated current	32 A
Thermal protection nob setting xIN	1
Rating current 10°C according to IEC 60947	43.8 A
Rating current 15°C according to IEC 60947	42.5 A
Rating current 20°C according to IEC 60947	41.2 A
Rating current 25°C according to IEC 60947	39.8 A
Rating current 30°C according to IEC 60947	38.4 A
Rating current 35°C according to IEC 60947	36.9 A
Rating current 40°C according to IEC 60947	35.3 A
Rating current 45°C according to IEC 60947	33.7 A
Rating current 50°C according to IEC 60947	32 A
Rating current 55°C according to IEC 60947	30.1 A
Rating current 60°C according to IEC 60947	28.2 A
Rating current 65°C according to IEC 60947	26.1 A

Rating current 70°C according to IEC 60947	23.9 A
Breaking capacity on 1 pole for IT 230V NF 60947-2	18 kA
Rated ultimate short-circuit breaking capacity Icu under 230V AC IEC 60947-2	18 kA
Rated ultimate short-circuit breaking capacity Icu under 240V AC IEC 60947-2	18 kA
Range of the thermal adjustment	32 A
Rated ultimate short-circuit breaking capacity Icu under 220V AC IEC 60947-2	18 kA

Dimensions

Depth of installed product	68 mm
Height of installed product	130 mm
Width of installed product	25 mm

Frequency

Frequency	50 to 60 Hz
-----------	-------------

Power

Total power loss under I _N	3 W
Power loss per pole at I _n	3 W

Endurance

Electric endurance in number of cycles	1000
Number of mechanical operations	4000

Installation, mounting

Tightening torque	6Nm
-------------------	-----

Connection

Connection cross-sect. flexible conductor	6 / 70mm ²
Connection cross-sect. rigid cable	6 / 95mm ²
Type of connection	with screw

Cable

Cable Material	Cu
----------------	----

Settings

Range of the magnetic adjustment	600 A
----------------------------------	-------

Equipment

Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0
Can be accessorized	Yes

Use cases

Category of use	A
-----------------	---

Standards

Subject to technical modifications

Safety

REACH conform	Yes
RoHS conform	Yes
Halogen free	No

Use conditions

Degree of pollution according to IEC 60664 / IEC 60947-2	3
Altitude	2000 m

temperatur

Temperature of calibration	50 °C
----------------------------	-------