



HDA063U

Moulded Case Circuit Breaker h3 x160 TM ADJ 3P3D 63A 18kA CTC

Technical characteristics

Architecture

Neutral position	without neutral
Number of protected poles	3
Number of poles	3 P
Type of pole	3P3D

Functions

Trip Unit	TM A/F
Integrated earth fault protection	No
Concurrently switching N-neutral	No

Controls and indicators

Motor drive integrated	No
------------------------	----

Main electrical features

Rated operational voltage Ue	220 / 415 V
Frequency	50/60 Hz

Voltage

Rated insulation voltage	690 V
Rated impulse withstand voltage	8 kV
With under voltage release	No

Electric current

Rated current	63 A
Thermal protection nob setting xIN	0.63 / 0.8 / 1
Rating current 10°C according to IEC 60947	71.7 A
Rating current 15°C according to IEC 60947	70.7 A
Rating current 20°C according to IEC 60947	69.6 A
Rating current 25°C according to IEC 60947	68.6 A
Rating current 30°C according to IEC 60947	67.5 A
Rating current 35°C according to IEC 60947	66.4 A
Rating current 40°C according to IEC 60947	65.3 A
Rating current 45°C according to IEC 60947	64.1 A
Rating current 50°C according to IEC 60947	63 A
Rating current 55°C according to IEC 60947	61.8 A
Rating current 60°C according to IEC 60947	60.6 A
Rating current 65°C according to IEC 60947	59.3 A
Rating current 70°C according to IEC 60947	58.1 A

Rated ultimate short-circuit breaking capacity Icu under 230V AC IEC 60947-2	25 kA
Rated ultimate short-circuit breaking capacity Icu under 240V AC IEC 60947-2	25 kA
Rated ultimate short-circuit breaking capacity Icu under 400V AC IEC 60947-2	18 kA
Rated ultimate short-circuit breaking capacity Icu under 415V AC IEC 60947-2	18 kA
Range of the thermal adjustment	40 / 50 / 63 A
Rated ultimate short-circuit breaking capacity Icu under 380V AC IEC 60947-2	18 kA

Dimensions

Depth of installed product	68 mm
Height of installed product	130 mm
Width of installed product	75 mm

Frequency

Frequency	50 to 60 Hz
-----------	-------------

Power

Power loss per pole at 0.63*In	4 W
Power loss per pole at 0.8*In	6.3 W
Total power loss at 0.63*In	12.1 W
Total power loss at 0.8*In	18.9 W
Total power loss under IN	30 W
Power loss per pole at In	10 W

Endurance

Electric endurance in number of cycles	1000
Number of mechanical operations	4000

Connection

Type of connection	with screw
--------------------	------------

Settings

Range of the magnetic adjustment	1000 A
----------------------------------	--------

Equipment

Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0
Can be accessorized	Yes

Standards

Standard text	IEC 60947-2
European directive WEEE	concerned

Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
Halogen free	No
Use conditions	
Degree of pollution according to IEC 60664 / IEC 60947-2	3
Altitude	2000 m
temperatur	
Temperature of calibration	50 °C