



HED400G

### **h3 MCCB h630 3x400A Plug In 70kA**

#### **Technical characteristics**

##### **Architecture**

Number of poles	3 P
-----------------	-----

##### **Functions**

Complete device with protection unit	Yes
Trip Unit	LSI
Integrated earth fault protection	No

##### **Configuration**

Number of modules	8
-------------------	---

##### **Main electrical features**

Rated operational voltage Ue	220 / 690 V
Frequency	50/60 Hz

##### **Voltage**

Rated insulation voltage	800 V
Rated impulse withstand voltage	8 kV
With under voltage release	No

##### **Electric current**

Rated current	400 A
Rated ultimate short-circuit breaking capacity Icu under 690V AC IEC 60947-2	20 kA
Thermal protection nob setting xIN	0.4 / 0.5 / 0.63 / 0.9 / 0.95 / 1
Breaking capacity on 1 pole for IT 230V NF 60947-2	60 kA
Breaking capacity on 1 pole for IT 400V NF 60947-2	9 kA
Rated service breaking capacity Ics AC according IEC 60947-2	71 %
Rated ultimate short-circuit breaking capacity Icu under 230V AC IEC 60947-2	100 kA
Rated ultimate short-circuit breaking capacity Icu under 240V AC IEC 60947-2	100 kA
Rated ultimate short-circuit breaking capacity Icu under 400V AC IEC 60947-2	70 kA
Rated ultimate short-circuit breaking capacity Icu under 415V AC IEC 60947-2	70 kA
Rated ultimate short-circuit breaking capacity Icu under 440V AC IEC 60947-2	65 kA

##### **Current correction factors**

Correction factor of rating current for 2 devices placed side-by-side	1
Correction factor of rating current for 3 devices placed side-by-side	1
Correction factor of rating current for 4 and 5 devices placed side-by-side	1
Correction factor of rating current for 6 devices placed side-by-side	1

#### Power

Total power loss under IN	86.4 W
Power loss per pole at In	28.8 W

#### Tripping

Trip mode	LSI
Thermal protection trip time	5 / 10 / 11 / 19 / 21 / 29 ms
Time of response when opening	10 ms

#### Electrical specifications

Magnetic trip delay time	100 to 200 ms
--------------------------	---------------

#### Endurance

Electric endurance in number of cycles	1000
Number of mechanical operations	4000

#### Installation, mounting

DIN rail mounting with optional adaptator	No
-------------------------------------------	----

#### Connection

Connection cross-sect. rigid cable	35 / 240mm <sup>2</sup>
Type of connection	Terminal

#### Settings

Range of the magnetic adjustment	2240 / 2800 / 3500 / 4480 / 5040 / 5200 / 5200 A
Magnetic protection nob setting xIN	2.5 / 5 / 10
Setting type In or Ith	IrTh

#### Equipment

Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0
Motor drive optional	Yes

#### Use cases

Category of use	A
-----------------	---

#### Standards

Standard text	IEC 60947-2
European directive WEEE	concerned

#### Use conditions

Operating temperature	-25...70 °C
Altitude	2000 m
Storage/transport temperature	-35...70 °C