



HEW631JR

**Moulded Case Circuit Breaker h3+ P630 LSI 4P4D N0-50-100% 630A 70kA FTC**

**Technical characteristics**

**Architecture**

Neutral position	left
Number of protected poles	4
Number of poles	4 P
Fixing mode	fixing plate
Type of case	Fixed built-in

**Functions**

Complete device with protection unit	Yes
Version as main switch	Yes
Version as emergency stop installation	No
Version as safety switch	No
Version as maintenance-/service switch	Yes
Trip Unit	LSI
Integrated earth fault protection	No
Concurrently switching N-neutral	Yes

**Controls and indicators**

Motor drive integrated	No
------------------------	----

**Main electrical features**

Rated operational voltage Ue	220 / 690 V
Type of supply voltage	AC
Frequency	50/60 Hz

**Voltage**

Rated insulation voltage	800 V
Rated impulse withstand voltage	8 kV
With under voltage release	No

**Electric current**

Rated current	630 A
Rated ultimate short-circuit breaking capacity Icu under 690V AC IEC 60947-2	12 kA
Rating current 10°C according to IEC 60947	630 A
Rating current 15°C according to IEC 60947	630 A
Rating current 20°C according to IEC 60947	630 A
Rating current 25°C according to IEC 60947	630 A
Rating current 30°C according to IEC 60947	630 A
Rating current 35°C according to IEC 60947	630 A

Rating current 40°C according to IEC 60947	630 A
Rating current 45°C according to IEC 60947	630 A
Rating current 50°C according to IEC 60947	630 A
Rating current 55°C according to IEC 60947	630 A
Rating current 60°C according to IEC 60947	622 A
Rating current 65°C according to IEC 60947	570 A
Rating current 70°C according to IEC 60947	510 A
Rated service breaking capacity Ics under 660V AC according IEC 60947-2	12 kA
Breaking capacity on 1 pole for IT 230V NF 60947-2	10 kA
Breaking capacity on 1 pole for IT 400V NF 60947-2	10 kA
Breaking capacity on 1 pole for IT 415V NF 60947-2	10 kA
Rated ultimate short-circuit breaking capacity Icu under 230V AC IEC 60947-2	100 kA
Rated ultimate short-circuit breaking capacity Icu under 240V AC IEC 60947-2	100 kA
Rated ultimate short-circuit breaking capacity Icu under 400V AC IEC 60947-2	70 kA
Rated ultimate short-circuit breaking capacity Icu under 415V AC IEC 60947-2	70 kA
Rated ultimate short-circuit breaking capacity Icu under 220V AC IEC 60947-2	100 kA
Rated ultimate short-circuit breaking capacity Icu under 380V AC IEC 60947-2	70 kA
Rated ultimate short-circuit breaking capacity Icu under 660V AC IEC 60947-2	12 kA
<b>Dimensions</b>	
Depth of installed product	150 mm
Height of installed product	260 mm
Width of installed product	185 mm
<b>Frequency</b>	
Frequency	50 to 60 Hz
<b>Power</b>	
Power loss per pole at 0.63*In	25.4 W
Power loss per pole at 0.8*In	40.6 W
Total power loss at 0.63*In	76.2 W
Total power loss at 0.8*In	121.9 W
Total power loss under IN	190.5 W
Power loss per pole at In	63.5 W
<b>Tripping</b>	
Time of response when opening	10 ms
<b>Installation, mounting</b>	
DIN rail mounting with optional adaptator	No
Suitable for front mounting	No
Suitable for ground mounting	Yes

Subject to technical modifications

<b>Connection</b>	
Type of connection	Terminal
<b>Cable</b>	
Cable Material	Cu / Al
<b>Equipment</b>	
Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0
Motor drive optional	Yes
Can be accessorized	Yes
<b>Use cases</b>	
Category of use	A
<b>Standards</b>	
Standard text	IEC 60947-2
European directive WEEE	concerned
<b>Safety</b>	
REACH conform	No
RoHS conform	Yes
Halogen free	No
<b>Use conditions</b>	
Degree of pollution according to IEC 60664 / IEC 60947-2	3
Altitude	2000 m
<b>temperatur</b>	
Temperature of calibration	50 °C