



HHA023Z

## Moulded Case Circuit Breaker h3 x160 TM FIX 1P1D 25A 25kA CTC

### Technical characteristics

#### Architecture

Neutral position	without neutral
Number of protected poles	1
Number of poles	1 P

#### Functions

Trip Unit	TM F/F
Integrated earth fault protection	No
Concurrently switching N-neutral	No

#### Controls and indicators

Motor drive integrated	No
------------------------	----

#### Main electrical features

Rated operational voltage Ue	220 / 240 V
Type of supply voltage	AC
Frequency	50/60 Hz

#### Voltage

Rated insulation voltage	690 V
Rated impulse withstand voltage	8 kV
With under voltage release	No

#### Electric current

Rated current	25 A
Thermal protection nob setting xIN	1
Rating current 10°C according to IEC 60947	29.6 A
Rating current 15°C according to IEC 60947	29 A
Rating current 20°C according to IEC 60947	28.5 A
Rating current 25°C according to IEC 60947	27.9 A
Rating current 30°C according to IEC 60947	27.4 A
Rating current 35°C according to IEC 60947	26.8 A
Rating current 40°C according to IEC 60947	26.2 A
Rating current 45°C according to IEC 60947	25.6 A
Rating current 50°C according to IEC 60947	25 A
Rating current 55°C according to IEC 60947	24.3 A
Rating current 60°C according to IEC 60947	23.7 A
Rating current 65°C according to IEC 60947	23 A
Rating current 70°C according to IEC 60947	22.3 A

Rated ultimate short-circuit breaking capacity Icu under 230V AC IEC 60947-2	35 kA
Rated ultimate short-circuit breaking capacity Icu under 240V AC IEC 60947-2	35 kA
Rated ultimate short-circuit breaking capacity Icu under 400V AC IEC 60947-2	25 kA
Rated ultimate short-circuit breaking capacity Icu under 415V AC IEC 60947-2	25 kA
Range of the thermal adjustment	25 A
Rated ultimate short-circuit breaking capacity Icu under 380V AC IEC 60947-2	25 kA
<b>Dimensions</b>	
Depth of installed product	68 mm
Height of installed product	130 mm
Width of installed product	25 mm
<b>Frequency</b>	
Frequency	50 to 60 Hz
<b>Power</b>	
Total power loss under IN	4.3 W
Power loss per pole at In	4.3 W
<b>Endurance</b>	
Electric endurance in number of cycles	1000
Number of mechanical operations	4000
<b>Installation, mounting</b>	
Tightening torque	6Nm
<b>Connection</b>	
Connection cross-sect. rigid cable	6 / 95mm <sup>2</sup>
<b>Cable</b>	
Cable Material	Cu
<b>Settings</b>	
Range of the magnetic adjustment	600 A
<b>Equipment</b>	
Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0
Can be accessorized	Yes
<b>Use cases</b>	
Category of use	A
<b>Standards</b>	
Standard text	IEC 60947-2

European directive WEEE	concerned
-------------------------	-----------

**Safety**

REACH conform	Yes
RoHS conform	Yes
Halogen free	No

**Use conditions**

Degree of pollution according to IEC 60664 / IEC 60947-2	3
Altitude	2000 m

**temperatur**

Temperature of calibration	50 °C
----------------------------	-------