



HNA080U

Moulded Case Circuit Breaker h3 x160 TM ADJ 3P3D 80A 40kA CTC

Technical characteristics

Architecture

Neutral position	without neutral
Number of protected poles	3
Number of poles	3 P
Type of pole	3P3D

Functions

Trip Unit	TM A/F
Integrated earth fault protection	No
Concurrently switching N-neutral	No

Controls and indicators

Motor drive integrated	No
------------------------	----

Main electrical features

Rated operational voltage Ue	220 / 415 V
Frequency	50/60 Hz

Voltage

Rated insulation voltage	690 V
Rated impulse withstand voltage	8 kV
With under voltage release	No

Electric current

Rated current	80 A
Thermal protection nob setting xIN	0.63 / 0.8 / 1
Rating current 10°C according to IEC 60947	93.2 A
Rating current 15°C according to IEC 60947	91.6 A
Rating current 20°C according to IEC 60947	90.1 A
Rating current 25°C according to IEC 60947	88.5 A
Rating current 30°C according to IEC 60947	86.8 A
Rating current 35°C according to IEC 60947	85.2 A
Rating current 40°C according to IEC 60947	83.5 A
Rating current 45°C according to IEC 60947	81.7 A
Rating current 50°C according to IEC 60947	80 A
Rating current 55°C according to IEC 60947	78.1 A
Rating current 60°C according to IEC 60947	76.3 A
Rating current 65°C according to IEC 60947	74.4 A
Rating current 70°C according to IEC 60947	72.4 A

Rated ultimate short-circuit breaking capacity Icu under 230V AC IEC 60947-2	85 kA
Rated ultimate short-circuit breaking capacity Icu under 240V AC IEC 60947-2	85 kA
Rated ultimate short-circuit breaking capacity Icu under 400V AC IEC 60947-2	40 kA
Rated ultimate short-circuit breaking capacity Icu under 415V AC IEC 60947-2	40 kA
Range of the thermal adjustment	50 / 63 / 80 A
Rated ultimate short-circuit breaking capacity Icu under 380V AC IEC 60947-2	40 kA

Dimensions

Depth of installed product	68 mm
Height of installed product	130 mm
Width of installed product	75 mm

Frequency

Frequency	50 to 60 Hz
-----------	-------------

Power

Power loss per pole at 0.63*In	4.2 W
Power loss per pole at 0.8*In	6.6 W
Total power loss at 0.63*In	12.5 W
Total power loss at 0.8*In	19.9 W
Total power loss under IN	32.1 W
Power loss per pole at In	10.7 W

Endurance

Electric endurance in number of cycles	1000
Number of mechanical operations	4000

Connection

Type of connection	with screw
--------------------	------------

Settings

Range of the magnetic adjustment	1000 A
----------------------------------	--------

Equipment

Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0
Can be accessorized	Yes

Standards

Standard text	IEC 60947-2
---------------	-------------

Safety

REACH conform	Yes
RoHS conform	Yes

Halogen free No

Use conditions

Degree of pollution according to IEC 60664 /
IEC 60947-2 3

Altitude 2000 m

temperatur

Temperature of calibration 50 °C