



HNG200U

## Moulded Case Circuit Breaker h250 3P 50kA 200A TM

### Technical characteristics

#### Architecture

Number of poles	3 P
-----------------	-----

#### Functions

Complete device with protection unit	Yes
Trip Unit	TM A/A
Integrated earth fault protection	No

#### Configuration

Number of modules	6
-------------------	---

#### Main electrical features

Rated operational voltage Ue	220 / 690 V
Frequency	50/60 Hz

#### Voltage

Rated insulation voltage	800 V
Rated impulse withstand voltage	8 kV
With under voltage release	No

#### Electric current

Rated current	200 A
Rated ultimate short-circuit breaking capacity Icu under 690V AC IEC 60947-2	7.5 kA
Thermal protection nob setting xIN	0.63 / 0.8 / 1
Breaking capacity on 1 pole for IT 230V NF 60947-2	51 kA
Breaking capacity on 1 pole for IT 400V NF 60947-2	9 kA
Rated service breaking capacity Ics AC according IEC 60947-2	50 %
Rated ultimate short-circuit breaking capacity Icu under 230V AC IEC 60947-2	85 kA
Rated ultimate short-circuit breaking capacity Icu under 240V AC IEC 60947-2	85 kA
Rated ultimate short-circuit breaking capacity Icu under 400V AC IEC 60947-2	50 kA
Rated ultimate short-circuit breaking capacity Icu under 415V AC IEC 60947-2	50 kA
Rated ultimate short-circuit breaking capacity Icu under 440V AC IEC 60947-2	50 kA

#### Current correction factors

Correction factor of rating current for 2 devices placed side-by-side	1
Correction factor of rating current for 3 devices placed side-by-side	1
Correction factor of rating current for 4 and 5 devices placed side-by-side	1
Correction factor of rating current for 6 devices placed side-by-side	1

#### Power

Total power loss under I <sub>N</sub>	31.2 W
Power loss per pole at I <sub>N</sub>	10.4 W

#### Tripping

Trip mode	TM
Thermal protection trip time	0 ms
Time of response when opening	20 ms

#### Electrical specifications

Magnetic trip delay time	0 ms
--------------------------	------

#### Endurance

Electric endurance in number of cycles	1000
Number of mechanical operations	4000

#### Installation, mounting

DIN rail mounting with optional adaptator	No
---	----

#### Connection

Connection cross-sect. flexible conductor	35 / 150mm <sup>2</sup>
Type of connection	Terminal

#### Settings

Range of the magnetic adjustment	1200 / 1600 / 2000 / 2600 A
Magnetic protection nob setting xI <sub>N</sub>	6 / 8 / 10 / 13
Setting type I <sub>N</sub> or I <sub>th</sub>	I <sub>N</sub>

#### Equipment

Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0
Motor drive optional	Yes

#### Use cases

Category of use	A
-----------------	---

#### Standards

Standard text	IEC 60947-2
European directive WEEE	concerned

#### Use conditions

Operating temperature	-25...70 °C
Altitude	2000 m
Storage/transport temperature	-35...70 °C