



HNT101JR

Moulded Case Circuit Breaker h3+ P250 LSI 4P4D N0-50-100% 100A 40kA FTC

Technical characteristics

Architecture

Type of order	Toggle
Neutral position	left
Number of protected poles	4
Number of poles	4 P
Type of pole	4P4D N:0/50/100%
Fixing mode	fixing plate
Type of case	Fixed built-in

Functions

Complete device with protection unit	Yes
Reversing switch	No
Version as main switch	Yes
Version as emergency stop installation	No
Version as safety switch	No
Version as maintenance-/service switch	Yes
Trip Unit	LSI
Integrated earth fault protection	No
Concurrently switching N-neutral	Yes

Controls and indicators

Motor drive integrated	No
------------------------	----

Main electrical features

Rated operational voltage Ue	220 / 690 V
Type of supply voltage	AC
Frequency	50/60 Hz

Voltage

Rated insulation voltage	800 V
Rated impulse withstand voltage	8 kV
With under voltage release	No

Electric current

Rated current	100 A
Rated ultimate short-circuit breaking capacity Icu under 690V AC IEC 60947-2	6 kA
Rated short-time withstand current Icw t=0.4S 220-240 V AC according IEC 60947-2	2.5 kA
Rated short-time withstand current Icw t=0.4S 380-415 V AC according IEC 60947-2	2.5 kA

Rated short-time withstand current I_{cw} $t=0.4S$ 660-690 V AC according IEC 60947-2	2.5 kA
Rating current 10°C according to IEC 60947	100 A
Rating current 15°C according to IEC 60947	100 A
Rating current 20°C according to IEC 60947	100 A
Rating current 25°C according to IEC 60947	100 A
Rating current 30°C according to IEC 60947	100 A
Rating current 35°C according to IEC 60947	100 A
Rating current 40°C according to IEC 60947	100 A
Rating current 45°C according to IEC 60947	100 A
Rating current 50°C according to IEC 60947	100 A
Rating current 55°C according to IEC 60947	100 A
Rating current 60°C according to IEC 60947	100 A
Rating current 65°C according to IEC 60947	100 A
Rating current 70°C according to IEC 60947	100 A
Rated service breaking capacity I_{cs} under 660V AC according IEC 60947-2	6 kA
Breaking capacity on 1 pole for IT 230V NF 60947-2	2.5 kA
Breaking capacity on 1 pole for IT 400V NF 60947-2	2.5 kA
Breaking capacity on 1 pole for IT 415V NF 60947-2	2.5 kA
Rated ultimate short-circuit breaking capacity I_{cu} under 230V AC IEC 60947-2	50 kA
Rated ultimate short-circuit breaking capacity I_{cu} under 240V AC IEC 60947-2	50 kA
Rated ultimate short-circuit breaking capacity I_{cu} under 400V AC IEC 60947-2	40 kA
Rated ultimate short-circuit breaking capacity I_{cu} under 415V AC IEC 60947-2	40 kA
Rated service breaking capacity I_{cs} under 110-138V AC according IEC 60947-2	50 kA
Rated ultimate short-circuit breaking capacity I_{cu} under 220V AC IEC 60947-2	50 kA
Rated ultimate short-circuit breaking capacity I_{cu} under 380V AC IEC 60947-2	40 kA
Rated ultimate short-circuit breaking capacity I_{cu} under 660V AC IEC 60947-2	6 kA

Dimensions

Depth of installed product	97 mm
Height of installed product	165 mm
Width of installed product	140 mm

Frequency

Frequency	50 to 60 Hz
-----------	-------------

Power

Total power loss under I_N	7.2 W
Power loss per pole at I_N	2.4 W

Endurance

Electric endurance in number of cycles	10000
Number of mechanical operations	40000
Cover, door	
Interlockable	Yes
Installation, mounting	
Tightening torque	12Nm
DIN rail mounting with optional adaptor	Yes
Suitable for front mounting center	No
Suitable for front mounting	No
Suitable for ground mounting	Yes
Connection	
Connection cross-sect. flexible conductor	35 / 150mm ²
Connection cross-sect. rigid cable	35 / 185mm ²
Connection	Front connection
Type of connection	Terminal
Protection	
Instantaneous protection (Ii): type	adjustable
Cable	
Cable Material	Cu / Al
Equipment	
Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0
Motor drive optional	Yes
Can be accessorized	Yes
Use cases	
Category of use	A
Use	
Vibrations and shocks withstand	IEC 68068-2-52 Test FC
Standards	
Standard text	IEC 60947-2
European directive WEEE	concerned
Safety	
Protection index IP	IP4X
Use conditions	
Degree of pollution according to IEC 60664 / IEC 60947-2	3
Altitude	2000 m

temperatur

Temperature of calibration

50 °C